

## USF™ Ion Exchange Resin and Media Cross Reference Guide

Siemens is the largest distributor of ion exchange resin. We are able to supply you resin from all of the leading manufacturers, and are the largest stocking distributor of Dowex brand resin.

USF™ Brand	Amberlite Rohm & Haas	Lewatit LANXESS	Ionac® Sybron	Diaion® Mitsubishi	Dowex® Dow	Purolite®
<b>Weak Acid Cation</b>						
USF C-271	IRC-76	CNP-80			MAC-3 (Marathon® MAC-3)	C-106
USF C-281	IRC-86		CC	WK-40		C-105
<b>Strong Acid Cation</b>						
USF C-211	IR-120 (Amberjet® 1200)	(MonoPlus® S-100)	C-249	SK-1B	HCR-S (Marathon® C)	C-100
USF C-361	IR-122 (Amberjet® 1500)	(MonoPlus® S-200)	C-250	SK-110	HGR-W2 (Marathon® C-10)	C100X10
USF C-381	IR-200	(MonoPlus® SP-112)		PK-228	(Marathon® MSC)	C-150
<b>Weak Base Anion</b>						
USF A-399	IRA-96	(MonoPlus® MP-64)		WA-30	(Marathon® WBA-2)	A-100
USF A-444	IRA-67	VP OC 1072				A-845
<b>Strong Base Anion</b>						
USF A-244	IRA-410 (Amberjet® 4600)	(MonoPlus® M-600)	ASB-2	SA-20A	SAR (Marathon® A2)	A-300
USF A-284	IRA-400 (Amberjet® 4200)	(MonoPlus® M-500)	ASB-1	SA-10A	SBR-C (Monosphere® 550A)	A-600
USF A-464	IRA-402 (Amberjet® 4400)		ASB-1P	SA-12A	SBR-P (Marathon® A)	A-400
USF A-674	IRA-900	(MonoPlus® MP-500)	A-641	PA-312	(Marathon® MSA)	A-500
A-714	IRA-458	VP OC 1071				A-850
<b>Mixed Bed</b>						
USF TM-9						NRW-37
USF EDM						
USF NR-6	IRN-150	SM 94	NM-60		(Marathon® MR-3)	
USF NR-14			NM-73			NRW-37
USF NR-30						EX MB
<i>( ) indicates Uniform Particle Size Equivalent</i>						

### ORDERING INFORMATION

Please contact Technical Support at, 800.875.7873 ext 5000 for more information.