



## Polypropylene Plastic Filter Housings

These filter housings are molded from polypropylene, and are available in 10 and 20 inch lengths. Housings are supplied with 3/4" inlet and outlets in standard flat gasket design for Code F filter cartridges. Heads are available with double cap plug design and Viton® o-rings.

- Durable housings are made from all polypropylene materials
- Housings contain no fillers, colorants, plasticizers, or lubricants
- Housings are autoclavable, ETO sterilizable, and hydrogen peroxide compatible
- Supplied with 3/4" NPT inlet and outlets in standard flat gasket design for Code F filter cartridges

### FILTER HOUSING SPECIFICATIONS

Dimensions	3.5" ID, 5 1/8" OD maximum
Materials	polypropylene cap and housing with standard Viton® E-60 o-rings
Maximum Operating Pressure	125 psi (8.6 bar)
Maximum Operating Temperature	100°F (38°C)
Sterilization/Sanitization	
Hydrogen Peroxide	7.5% compatibility; static soak up to 24 hr at ambient temperature
Weight	
10" housing	3 lb (1.4 kg)
20" housing	4.25 lb (1.9 kg)
<i>Housing Compatibility/Cartridge Type</i>	
ZHCFA1001	Code F, 9 3/4"
ZHCFA2001	Code F, 20"

### ORDERING INFORMATION

<i>Catalog Number:</i>	<b>ZHC</b>	<b>F</b>	<b>A</b>	<b>XX</b>	<b>XX</b>
System Name	Polypropylene filter housing				
Cartridge Code		F = Code F			
Cartridge Configuration			A = No plugs	10 = 10	
Length				20 = 20	
Number of Tubes					01 = 1 tube

To figure your order number, replace the X with one of the numbered options below it.

### ACCESSORIES

<i>Description</i>	<i>Catalog Number</i>
Mounting Bracket	ZHA150060
Wrench	FC150295
O-ring replacement	ZHA151021