



TYPICAL DESIGN

MATERIAL: 316 SS
 END CONNECTIONS CAN BE
 MODIFIED TO SUIT.

DESIGN SPECIFICATIONS:

FLOW RATE	-----	4 MINIMUM
(GPM)		11 CONTINUOUS
		17 INTERMITTENT
RESIN VOLUME	-----	3 CU.FT.
BED AREA	-----	1.4 SQ.FT.
DESIGN PRESSURE	-----	125 PSIG CODE
TEMPERATURE	-----	100°F
WEIGHT	-----	250 SHIPPING
(LBS)		450 OPERATING

PERMUTIT POWER PRODUCTS
 XP-16 NON-REGENERABLE
 DEMINERALIZER



IP&S
 BRIDGEWATER N.J.
 (908) 704-9027