


1 1/4" SLUICE IN 1 1/2" WATER IN



TYPICAL DESIGN

CONNECTIONS SHOWN AS FLANGED. OTHER ENDS ALSO AVAILABLE AS PIPE TAPS, COUPLINGS PLAIN ENDS FOR WELDING

ION EXCHANGE RESIN OR OTHER BED MATERIAL (OPTIONAL)

61" APPROX.

30" O.D.

7"

1 1/4" SLUICE OUT 1 1/2" WATER OUT

DESIGN SPECIFICATIONS:

FLOW RATE	-----	12 MINIMUM
(GPM)		-40 CONTINUOUS
		-60 INTERMITTENT
MAXIMUM RESIN VOLUME	----	15 CU.FT.
BED AREA	-----	4.9 SQ.FT.
DESIGN PRESSURE	-----	125 PSIG NC
TEMPERATURE	-----	100°F
WEIGHT	-----	400 SHIPPING
(LBS)		-1300 OPERATING

PERMUTIT POWER PRODUCTS
XP-30 NON-REGENERABLE
DEMINERALIZER



IP&S
BRIDGEWATER N.J.
(908) 704-9027