

Replacement Cartridge kits for Barnstead® Laboratory Water Systems

ORDERING INFORMATION

Replacement Cartridge Kits for NANOpure™ and Other Barnstead Systems

Description	Where Used	Barnstead Equiv. Part Number	Siemens Catalog Number
1 ea. CW0835 Colloid Removal Resin, 1 ea. CW0803 High Capacity 2-Bed Resin, 2 ea. CW0809 Mixed Bed	NANOpure 4 Module Type I	D3804	CW3804
1 ea. CW0835 Colloid Removal Resin, 2 ea. CW0809 Mixed Bed	NANOpure 3 Module Type I	D3805	CW3805
1 ea. CW0836 Organic Removal, 1 ea. CW0820 Organic Scavenger, 1 ea. CW0809 Mixed Bed	NANOpure 3 Module Type I w/ORGANICfree™	D3806	CW3806
1 ea. CW0836 Organic Removal, 1 ea. CW0803 High Capacity 2-Bed Resin, 1 ea. CW0809 Mixed Bed, 1 ea. CW0820 Organic Scavenger,	NANOpure 4 Module Type I w/ORGANICfree	D3807	CW3807
1 ea. CW0835 Colloid Removal Resin, 1 ea. CW0803 High Capacity 2-Bed Resin, 2 ea. CW5027 Mixed Bed	Quad Style NANOpure Type I	D4801	CW4801
1 ea. CW0836 Organic Removal, 1 ea. CW0803 High Capacity 2-Bed Resin, 1 ea. CW5027 Mixed Bed, 1 ea. CW5021 Organic Scavenger, Down Flow	Quad Style NANOpure Type I w/ORGANICfree	D4802	CW4802
1 ea. CW0835 Colloid Removal Resin, 1 ea. CW0809 Mixed Bed, 2 ea. CW5027 Mixed Bed, 2 ea. CW3751 Final Filter	Quad Style NANOpure Type I w/ORGANICfree Pretreated Feed	D5025	CW5025
1 ea. CW0836 Colloid Removal, 1 ea. CW0809 Mixed Bed, 1 ea. CW5021 Organic Scavenger, Down Flow, 1 ea. CW5027 Mixed Bed, 2 ea. CW3751 Final Filter	Quad Style NANOpure Type I w/ORGANICfree Pretreated Feed	D5026	CW5026
1 ea. CW0835 Colloid Removal Resin, 1 ea. CW0803 High Capacity 2-Bed Resin, 2 ea. CW5027 Mixed Bed	E-pure™ 4 Module Type I	D5028	CW5028
1 ea. CW0835 Colloid Removal Resin, 2 ea. CW5027 Mixed Bed	E-pure 3 Module Type I	D5029	CW5029
1 ea. CW0836 Organic Removal, 1 ea. CW5027 Mixed Bed, 1 ea. CW5021 Organic Scavenger, Down Flow	E-pure 3 Module Type I w/ORGANICfree	D5022	CW5022
1 ea. CW0836 Organic Removal, 1 ea. CW0803 High Capacity 2-Bed Resin, 1 ea. CW5027 Mixed Bed, 1 ea. CW5021 Organic Scavenger, Down Flow	E-pure 4 Module Type I w/ORGANICfree	D5023	CW5023

Barnstead replacement cartridges continued on next page



Replacement Cartridges for Barnstead® Laboratory Water Systems

ORDERING INFORMATION

Replacement Cartridge Kits for NANOpure™ and Other Barnstead Systems

Description	Where Used	Barnstead Equiv. Part Number	Siemens Catalog Number
High Capacity, 2-Bed Ion Exchange	NANOpure, E-pure™, B-pure™, Cooling Loops	D0803	CW0803
Mixed Bed Ion Exchange	NANOpure, B-pure, Older NANOpure Cooling Loops	D0809	CW0809*
Oxygen Removal Resin	B-pure, Cooling Loops	D0811	CW0811
Activated Carbon	B-pure, Cooling Loops	D0813	CW0813
Cation Removal Resin	B-pure, Cooling Loops	D0815	CW0815
Organic Scavenger Resin	NANOpure II, Older NANOpure Systems	D0820	CW0820
Organic Scavenger, Down Flow	Quad Style NANOpure, E-pure	D5021	CW5021
Mixed Bed, Organic Removal	B-pure, Still Pretreatment	D0832	CW0832
Colloid, Organic Removal	NANOpure, B-pure, E-pure	D0835	CW0835
Organic Removal	NANOpure, E-pure, Pretreatment for Organic Removal	D0836	CW0836
Oxygen Removal	B-pure, Cooling Loops	D8809	CW8809
Mixed Bed, Oxygen Removal, Organic Removal	B-pure, Cooling Loops	D8811	CW8811
Anion Removal	B-pure, Cooling Loops	D0760	CW0760
Mixed Bed, Down Flow	Quad Style NANOpure, E-pure	D5027	CW5027
Organic Free Cartridge	NANOpure Infinity®	D50252	CB50252
Organic Cartridge Kit DI Feed	NANOpure Infinity	D50254	CB50254
Pretreat Cartridge for Tap & DI Feed	NANOpure Infinity	D50251	CB50251
Ultrapure Cartridge	NANOpure Infinity	D50253	CB50253
Cartridge Kit for RO or Dist. Feed	NANOpure Infinity	D50257	CB50257
Pretreatment DI Feed	EASYpure®	D50230	CB50230
Ultrapure Cartridge	EASYpure	D50233	CB50233
0.2µm Filter	EASYpure	FL703X2	CB7033X2
Organic Free Cartridge	EASYpure	D50229	CB50229
Pretreatment Cartridge for Dist. or RO Feed	EASYpure	D50231	CB50231
Ultralow Organics Cartridge for RO or Dist. Feed	Diamond™	D50280	CB50280
Cartridge Pack Organic Free for DI Feed	Diamond	D50281	CB50281
Sanitization Cartridge	NANOpure®, G-pure, NANOpure Infinity®	D50223	CB50223
Sanitization Cartridge	NANOpure®, G-pure, NANOpure Infinity®	D50258	CB50258
5µm Cartridge	Diamond RO, Diamond TII	D502113	CB502113
Sanitization Cartridge	EASYpure	D50245	CB50245
Cartridge for RO Feed	Diamond	D50282	CB50282
Cartridge Kit for DI Feed	Diamond	D50283	CB50283

* CW0809 — not for use with Bantam deionizers

Reverse Osmosis Membrane	ULTROpure™ and ROpure™ LP	D2732	CB2732
DI Cartridge	EASYpure® II and RF/UV	D3750	CW3750
Remote Dispenser Cross Flow Final Filter Quad Style	Final Filters	D3751	CW3751
Replacement Ultrafilter Element for D4721	Final Filters	D4722	CB4722
Ultrapure Ion Exchange	NANOpure® Quad., E-pure	D5021	CB5021
RO MPS Cartridge	NANOpure® Diamond™ RO	D502114	CB502114
Carbon Filter	NANOpure® Diamond™ RO	D502115	CB502115
Deionization	EASYpure® Systems	D50229	CB50229
Deionization	EASYpure® II LF and UV	D50245	CB50245
Prefilter, 5µm	ROpure™ Infinity	D9004	CB9004
Pretreatment Carbon Cartridge	ROpure™ Infinity	D9005	CB9005
Membrane 15L/hr	ROpure™ Infinity	D9006	CB9006
RO Membrane	NANOpure® Diamond™ RO	FL1265X1	CBFL1265X1
UF Cartridge	NANOpure® Diamond™ RO	FL1192X1	CBFL1192Y1



Replacement Cartridges for Barnstead® Laboratory Water Systems

Replacement Hose Nipple Cartridge Kits for Barnstead and Other Cartridge Housings

Description	Where Used	Barnstead Equiv. Part Number	Siemens Catalog Number
1/2 Size, Mixed Bed Oxygen Removal	180 Grains as CaCO ₃	D8822	CW8822
High Capacity, 2 Bed	1650 Grains as CaCO ₃	D8901	CW8901
Mixed Bed	730 Grains as CaCO ₃	D8902	CW8902
Pretreatment	1450 Grains as NaCl to 1 megohm-cm Endpoint	D8921	CW8921
Organic Removal		D8904	CW8904
Mixed Bed (No Dye)	730 Grains as CaCO ₃	D8911	CW8911
Organic Removal, Mixed Bed	575 Grains as CaCO ₃	D8922	CW8922
2/3 Size, High Capacity Mixed Bed	1080 Grains as CaCO ₃	D8950	CW8950

Note: Hose Nipple Cartridges are non-pressure applications; outlet must be vented to atmosphere, minimum inlet pressure should be 5 psig (0.3 bar) and designed for 3/8" H.B. (9.5mm) connection.

