

Material Safety Data Sheet

SECTION 1 – CHEMICAL PRODUCT AND COMPANY INFORMATION

Product: Bioxide® Plus 71

Chemical Family: Odor Control Compound

Manufacturer's Name: Siemens Industry, Inc. - Water Technologies Business Unit

Address: 2650 Tallevast Road, Sarasota, FL 34243

Product/Technical Information Phone Number: (941) 355.2971

Medical/Handling Emergency Phone Number: CHEMTREC (800) 424.9300
24 hours a day

Transportation Emergency Phone Number: CHEMTREC (800) 424.9300
24 hours a day

Issue Date: April 2009

Revision Number / Date: Rev 2 April 2011

SECTION 2 – COMPOSITION INFORMATION

<u>Chemical Name</u>	<u>Percent by Weight</u>	<u>CAS#</u>
Calcium Nitrate Tetrahydrate	30-70	13477-34-4
Sodium chlorite	<2.8	7758-19-2
Water	Balance	7732-18-5

SECTION 3 – HAZARDS IDENTIFICATION

Appearance & Odor: Colorless to amber liquid with a slight chlorine odor.

Emergency Overview: Spills will make the floor slippery. Do not allow the product to evaporate to dryness as the dry residue can ignite upon contact with combustible materials.

Fire & Explosion Hazards: Not flammable.

Primary Route(s) of Exposure: Skin and eye contact, and inhalation.

Inhalation – Acute Effects: Inhalation of vapors or mists may cause irritation to the respiratory tract. Breathing vapor or mists may be harmful.

Skin Contact – Acute Effects: Occasional brief contact with the liquid is not expected to result in significant irritation. Prolonged contact may cause irritation.

Eye Contact – Acute Effects: Eye contact will irritate and may burn the eyes.

Ingestion – Acute Effects: May be harmful if swallowed. May cause gastrointestinal irritation and nausea.

SECTION 4 – FIRST AID MEASURES

Inhalation First Aid: Remove affected person to fresh air. Give artificial respiration ONLY if breathing has stopped. Obtain medical attention.

Material Safety Data Sheet

Skin Contact First Aid: Immediately remove clothing from affected area and wash skin with flowing water and soap. Clothing should be washed before reuse. Obtain medical attention if irritation persists.

Eye Contact First Aid: Immediately irrigate eyes with flowing water continuously for 15 minutes while holding eyes open. Contacts should be removed before or during flushing. Obtain medical attention if irritation develops.

Ingestion First Aid: If victim is alert, rinse mouth with water and give water to drink. Do not induce vomiting. If spontaneous vomiting occurs, have affected person lean forward with head down to avoid breathing in vomitus. Rinse mouth again and give more water to drink. Obtain medical attention immediately.

Medical Conditions Aggravated: Pre-existing disorders of the following organs or systems include: respiratory system (including asthma and other breathing disorders), and gastrointestinal system.

Note to Physician: Chlorine dioxide vapors are emitted when this product contacts acids or chlorine. If these vapors are inhaled, monitor the patient closely for delayed development of pulmonary edema which may occur up to 48-72 hr after inhalation.

SECTION 5 – FIRE FIGHTING MEASURES

Flash Point/Method: Not applicable

Auto Ignition Temperature: Not applicable

Upper/Lower Explosion Limits: Not applicable

Extinguishing Media: Use extinguishing agent suitable for the surrounding fire.

Fire Fighting Procedures: Firefighters should wear full protective clothing and a NIOSH/OSHA approved positive pressure self-contained breathing apparatus. Approach fire from upwind to avoid hazardous vapors and toxic decomposition products. Use flooding quantities of water as fog or spray. This product becomes a fire or explosion hazard if allowed to dry, so use water spray to keep fire-exposed containers cool.

Fire & Explosion Hazards: If this product is allowed to dry it can ignite upon contact with combustible materials.

Hazardous Products of Decomposition and/or Combustion: Gaseous oxides of sodium and nitrogen when heated above the melting point of the solid 306.8° C.

NFPA Ratings: HEALTH -1 FLAMMABILITY - 0 REACTIVITY - 1

Material Safety Data Sheet

SECTION 6 – ACCIDENTAL RELEASE MEASURES

Wear appropriate personal protective equipment (See Section 8). Stop leak if safe to do so without risk. Ventilate area. If safe to do so, absorb spill with inert material, (e.g., dry sand or earth), then place into a chemical waste container. Do not use organic materials, such as wood shavings, wood dust or paper, to absorb spills. Flush area with flooding amounts of water. **DO NOT DUMP ON THE GROUND OR INTO ANY BODY OF WATER.** All disposal methods must be in compliance with all Federal, State, Local and Provincial laws and regulations. Regulations may vary in different locations. Waste characterizations and compliance with applicable laws are the responsibility solely of the waste generator.

SECTION 7 – HANDLING AND STORAGE

Handling: Wash thoroughly after handling. Use with adequate ventilation. Do not get in eyes, on skin, or on clothing. Do not breathe mists or vapors. Wear all recommended personal protective equipment (See Section 8).

Storage: Protect from physical damage and freezing. Store in a cool well ventilated place away from incompatible materials such as combustible, organic, or other readily oxidizable materials. Avoid storage on wood floors. Keep containers tightly closed. Do not store in very warm areas where the liquid may evaporate.

SECTION 8 –PERSONAL PROTECTION/ EXPOSURE CONTROL

Respiratory Protection: If use conditions generate mists or vapors, wear a NIOSH-approved respirator with acid gas canisters.

Skin Protection: Wear rubber gloves and other protective clothing such as coveralls and rubber boots as appropriate to prevent skin contact. Wear a rubber apron if splashing is likely.

Eye Protection: Wear chemical goggles. In addition, wear a faceshield when connecting and disconnecting piping or if splashing is likely.

Ventilation Protection: General exhaust ventilation under normal use conditions. If vapors or mist are generated use local exhaust ventilation.

Other Protection: Recommend means of washing the eyes with a gentle flow of cool to tepid water be readily available in all areas where this material is handled or stored. Employees should wash their hands and face before eating, drinking, or using tobacco products.

Exposure Limits: Exposure limits have not been established for this product or its components.

SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Boiling Point: > 212 °F

Freezing Point: < 25 °F

Specific Gravity: 1.4 – 1.5 at 70 °F

Solubility in Water: Complete

Volatile Percentage: 30%

pH: 8.0 – 10.0

Material Safety Data Sheet

SECTION 10 – STABILITY AND REACTIVITY

Stability: This product is stable under normal use conditions.

Incompatibilities: Avoid contact with wood and other flammable organics, flammable or combustible materials, cyanides, sodium hypophosphite, or boron phosphide.

Polymerization: Hazardous polymerization will not occur.

Decomposition: After water has evaporated, this material may thermally decompose producing oxides of nitrogen. Explosive and toxic chlorine dioxide gas will be generated on contact with acids or chlorine.

Conditions to Avoid: Do not allow to evaporate to dryness. Do not heat to 1000° F as an explosion may occur in the presence of reducing agents or inorganic materials.

SECTION 11 – TOXICOLOGICAL INFORMATION

Toxicological Data: Not established for this product. However, for its components:

Calcium nitrate: Oral (rat) LD50 = 302 mg / kg

Sodium chlorite: Oral (rat) LD50 = 165 mg / kg

Chronic Effects: The toxicity of nitrates is due to their in vivo conversion to nitrites which may lead to methemoglobinemia. Sodium nitrate may react with secondary and tertiary amines to form nitrosamines, some of which are suspect cancer agents.

Mutagenicity: Sodium chlorite, a minor component of this material, has tested positive in some studies with laboratory animals. The significance of these results for human health is unclear because the oxidizing effects of the chlorite or the salty effects of the sodium may significantly affect the ability of the tests to accurately detect mutagens.

Carcinogenicity: There are no known carcinogenic effects of this product.

Neurotoxicity: No data available for this product or its components.

Other Effects: The substance may cause effects on the blood, resulting in formation of methemoglobin when ingested.

Target Organs: Target organs include the skin, eyes, digestive tract and respiratory system.

SECTION 12 – ECOLOGICAL INFORMATION

The ecological effects are not known. Safely store product to prevent release to the environment and water supplies.

SECTION 13 – DISPOSAL CONSIDERATIONS

Material that cannot be used, or chemically reprocessed for use, and empty containers should be disposed of in accordance with all applicable regulations. Product containers should be thoroughly emptied before disposal. Generators of waste material are required to evaluate all

Material Safety Data Sheet

waste for compliance with RCRA and any local disposal procedures and regulations. NOTE: State and local regulations may be more stringent than federal regulations.

SECTION 14 – TRANSPORTATION INFORMATION

Domestic Transportation: This material is not considered a hazardous material for domestic transportation purposes.

International Transportation: This material is not considered a dangerous good for international transportation purposes.

SECTION 15 – REGULATORY INFORMATION

OSHA HAZARD COMMUNICATION STANDARD: Health hazard

CERCLA HAZARDOUS SUBSTANCE No RQ: None

SARA SECTION 311/312:

Acute Health = Yes

Chronic Health = No

Fire = No

Pressure Release = No

Reactivity = No

SARA SECTION 313: No

OSHA PROCESS SAFETY (29CFR1910.119): No

CALIFORNIA PROPOSITION 65: Not listed.

SECTION 16 – OTHER INFORMATION

Disclaimer: The information contained herein is based on data considered accurate. However, no warranty is expressed or implied regarding the accuracy of these data or the results to be obtained from the user thereof. It is the buyer's responsibility to ensure that its activities comply with federal, state, provincial and local laws.

Revision Indicator: Legal Entity name change 04/01/11