

Cartridge Filters and Accessories

Water Technologies

SIEMENS

At Siemens Water Technologies, our mission is to provide products and services to meet your water treatment needs, any time, any place. As one of the world's largest water treatment companies, we offer a wide range of products and services, combined with experience and technical knowledge you can trust. We will deliver a solution that meets even the most stringent specifications. And, because your satisfaction is important to us, we stand behind the quality of our products and services.







Products

TABLE OF CONTENTS

CARTRIDGE FILTERS	
Cartridge End Caps	4
Activated Carbon Filters	
Granular Activated Carbon	5
Pulverized Activated Carbon	6
Particulate Cartridges	
DI Gard™ String Wound	7
ROGARD™ Graded Density Polypropylene	8
Prepure DP™ Graded Density Polypropylene Depth	9
NT Series Graded Pore Polypropylene Depth	10
Postpure PP™ Graded Density Pleated Polypropylene Depth	11
NA Series Absolute Rated Polypropylene Depth	12
WN Series Pleated Polysulfone Membrane	13
WE Series Pleated Polysulfone Membrane	14
DI Series Pleated Hydrophilic PVDF Media	15
PV Series Pleated Hydrophilic PVDF Media	16
VH Series Pleated PES Media Pharmaceutical Grade	17
UF Series Hollow Fiber Polysulfone Media	18
Housings	
316 Stainless Steel, Single Tube (Code F)	19
316L Stainless Steel, Single Tube (Code O)	20
316L Electropolished Stainless Steel, Multi-tube	21
316L Stainless Steel, Multi-tube (High-Purity)	22
316 Stainless Steel, Multi-tube	23
304 Stainless Steel, Multi-tube (with V Clamp closure)	25
304 Stainless Steel, Multi-tube (with Swing Bolt closure)	26
Polypropylene Plastic	27
White Polypropylene Plastic (Dialysis)	28
Natural Polypropylene Plastic	29
Speciality Cartridges	
CLERIFY™ Oil Adsorption	30
Vent Filter Cartridges	
Hydrophobic PTFE Media	31
EA Series Hydrophobic Polypropylene Media	32
VA Series Hydrophobic PTFE Media	33
VP Series Hydrophobic PTFE Media	34
TRADEMARK STATEMENT	35

Cartridge End Caps

The following table is presented as reference when ordering filter cartridges. For more detailed information, please contact our Technical Support Team at 800-875-7873 ext. 5000.

CARTRIDGE DESIGN	DESCRIPTION	CODE
 <p>Code F Style Cartridges Double open end with flat gasket</p>	Gaskets compressed on knife edge seal of housing	F
 <p>Code 10 Style Cartridges Single Open End with 1-120 Internal O-Ring at Open End</p>	Single O-ring located inside the cartridge	10
 <p>Code O Style Cartridges Single Open End with 2-222 O-Ring with Seal</p>	O-rings are located externally on the cartridge	0
 <p>Code 5 Style Cartridges Single Open End 2-222 O-Ring Seal and Spear End Assembly</p>	O-rings are located externally on the cartridge	5
 <p>Code 7 Style Cartridges Single Open End with 2-226 O-Ring Locking Seal and Spear End Assembly</p>	O-rings are located externally on the cartridge. The adapter locks into the housing with spear assembly	7
 <p>Code K SOE plastic spring assembly, saw cut end</p>	Knife edge SOE with spring seal	K





Granular Activated Carbon Filter Cartridge

- Composed of lignite-based granular activated carbon in an upflow cartridge design for removing chlorine feed water
- Cartridge is designed to allow water to enter the bottom of the cartridge, then filtered through the entire carbon bed before exiting at the top to maximize the contact time and therefore the adsorption
- Internal expansion pad maintains a tight, compact column to minimize channeling or bypass
- Nominal 20 micron post-filter reduces carbon fines as well as other suspended particles

SPECIFICATIONS

	10" Cartridge	20" Cartridge
Dimensions		
Diameter (OD)	2.875" (7.3 cm)	2.875" (7.3 cm)
Length (in)	9.75" (24.8 cm)	20" (50.8 cm)
Recommended Water Flow Rates		
10" Cartridge Maximum	1.0 gpm (3.8 lpm)	2.0 gpm (7.6 lpm)
Materials		
Filter Media	Granular, Activated Carbon	
Post filter	Spun Polypropylene	
Expansion Pad Foam	Polyether/Polyurethane	
Outer Casing	Polystyrene	
End Caps	Polystyrene	
Gaskets	Buna-N	
Operating Parameters		
Temperature Range	32 to 125°F (0 – 52°C)	
Carbon Volume	12 ounces of granular carbon per 10" length	

ORDERING INFORMATION

Catalog Number	Description
FCGC	Filter cartridge granular carbon
F	Cartridge Code: F = flat gasket seal
XX	Length (in): 10 = 10, 20 = 20
20	Nominal micron retention rating

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it.

Pulverized Activated Carbon Filter Cartridge



- Composed of pre-washed, finely pulverized activated carbon, encapsulated in a depth filtration media of highly purified alpha-cellulose and synthetic fibers for removing chlorine
- Depth-type cartridge ensures superior dirt holding capacity in sediment-laden waters to minimize premature exhaustion while it is being carbon treated
- Design includes a thermally bonded outer, nominal 10 micron pre-filtration layer that provides for depth filtration in one pass without carbon channeling or media migration

SPECIFICATIONS

Dimensions

Diameter (OD)
Length (in)

10" Cartridge

2.75" (7.0 cm)
9.75" (24.8 cm)

20" Cartridge

2.75" (7.0 cm)
20" (50.8 cm)

Recommended Water Flow Rates

Maximum

1.0 gpm (3.8 lpm) 2.0 gpm (7.6 lpm)

Materials

Primary filter media
Inner Layer Media
Inner Core
Outer Netting
End Caps

Pulverized, Activated Carbon
Alpha Cellulose and Synthetic Fibers
Polypropylene
Polyolefin
Low Durometer Polyethylene

Operating Parameters

Temperature Range . . .

32 to 125°F (0 – 52°C)

Carbon Volume

.

3.7 ounces of pulverized carbon per 10" length

ORDERING INFORMATION

Catalog Number	Description
FCPC	Filter cartridge pulverized carbon
F	Cartridge Code: F = double open end w/flat gasket seal
XX	Length (in): 10 = 10, 20 = 20
10	Nominal micron retention rating

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it.





DI GARD™ String Wound Prefiltration Cartridges

- Designed for a variety of prefiltration applications such as SDI (service deionization), reverse osmosis, and CDI® (Continuous Deionization) systems
- String wound type filter with your choice of cotton, industrial or surfactant-free polypropylene string over a polypropylene core
- Large void volume design for low-cost, reliable filtration performance with high contaminant holding capacity
- Continuous filter winding in 20-, 30-, and 40-inch lengths prevents by-passing or excessive pressure drops at the seams
- Gasketed end caps on 0.5 µm rated filters for positive sealing that eliminates by-passing
- Surfactant-free FCPX style filter meets USP Class VI Biological Tests for Plastics requirements

SPECIFICATIONS

Dimensions

Diameter (OD)
Length (in)

2.5" (6.5 cm)
9.75, 10, 19.5, 20, 29.25, 30, 40

Materials

FCCS
FCPS
FCPX

FDA-Listed bleached white cotton fiber string media with polypropylene core
FDA-Listed polypropylene fiber string media with polypropylene core
Surfactant-free polypropylene fiber string media with polypropylene core
NOTE: Code F cartridges (0.5 µm) have santophrene end seals.

Operating Parameters


Maximum Temperature
Maximum Differential Pressure @ 25°C
Micron Ratings
Filtration Efficiency

140°F (60°C)
50 psi (3.4 bar)
0.5, 1, 3, 5, 10, 20, 50 Microns
Nominal 90%

Recommended Water Flow Rates . .

5.0 gpm/10" length (18.9 lpm/10" length)

FLOW RATE vs. INITIAL CLEAN PRESSURE DROP



ORDERING INFORMATION

Catalog Number	Description
FCXX	FCCS = FDA-Listed bleached cotton string fiber FCPS = FDA-Listed polypropylene string fiber FCPX = surfactant-free polypropylene string fiber cartridge
F	Cartridge Code: F = double open end
XX	Length (in): 09 = 9.75, 10 = 10, 19 = 19.5, 20 = 20, 29 = 29.25, 30 = 30, 40 = 40
XX	Micron Rating: S5 = 0.5µm, 01 = 1 µm, 03 = 3 µm, 05 = 5 µm, 10 = 10 µm, 20 = 20 µm, 50 = 50 µm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.

ROGARD™ Graded Density Polypropylene Media Filter Cartridge

- Designed for a variety of prefiltration applications such as SDI (service deionization), reverse osmosis and CDI® (Continuous Deionization) systems
- Graded density melt spun polypropylene media design for exceptional throughput, with high contaminant holding capacity
- Gasketed end caps on 1, 3 and 5 µm rated filters for positive sealing that eliminates bypass contamination
- Manufactured from materials which are listed for food contact applications in Title 21 of the U.S. Code of Federal Regulations. Product in compliance with EU Directive 2002/72/EC for plastic in food contact (in simulants A, B, C, and D).
- All polypropylene components meet the specifications for biological safety as per the USP for Class VI-121 °C plastics (gaskets/O-rings excluded).
- FCRO Series filter cartridges are free of surfactants, anti-static agents, binders, and adhesives
- NSF Certified



SPECIFICATIONS

Dimensions

Diameter (OD)	2.5" (6.5 cm)
Length (in)	9.75, 10, 12, 19.5, 20, 30, 31, 40


Materials

Media	Melt blown polypropylene
Core	Integral polypropylene core
O-Rings	Silicone o-rings
Gaskets	Santoprene end seals

Operating Parameters

Maximum Temperature	140°F @ 25 psid
Maximum Differential Pressure @ 25°C	50 psi (3.4 bar)
Micron Ratings	1, 3, 5, 10, 20, 25, 50, 75 microns
Filtration Efficiency	Nominal 90%

Recommended Water Flow Rate 5.0 gpm/10" length (18.9 lpm/10" length)



ORDERING INFORMATION

Catalog Number and Description

FCRO	Rogard II all polypropylene depth cartridge
X	Cartridge Code: F = double open end (1&5 µm w/gasket) K = knife edge seal with spring seal O = 2-222 o-rings (12&20", 1&5 µm only) N = double open end (1, 3 & 5 µm – no gasket)
XX	Length (in): 09 = 9.75, 10 = 10, 12 = 12, 19 = 19.5, 20 = 20, 30 = 30, 31 = 31, 40 = 40
XX	Micron Rating: 01 = 1 µm, 03 = 3 µm, 05 = 5 µm, 10 = 10 µm, 20 = 20 µm, 25 = 25 µm, 50 = 50 µm, 75 = 75 µm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.



Siemens
Water Technologies
24-hr Customer Service: 800.466.7873



Prepure DP™ Graded Density Polypropylene Depth Media Filter Cartridge

- Composed of graded density melt blown polypropylene depth media for high efficiency prefiltration and post-filtration of DI resin applications
- Prepure DP™ filtration cartridges feature high contaminant loading due to graded density depth filtration media construction
- FDA Listed Materials - Manufactured from materials which are listed for food contact applications in Title 21 of the U.S. Code of Federal Regulations
- All components meet the specifications for biological safety as per the USP for Class VI-121 °C plastics (gaskets/O-rings excluded).
- Virgin polypropylene construction with fusion welding minimizes extractables

SPECIFICATIONS

Dimensions

Diameter (OD)
Length (in)

2.6" (6.6 cm)
9.75, 10, 20, 30, 40

Materials

Cartridge
Media
Seals

Polypropylene caps, core and cage
Non-woven melt blown polypropylene
Silicone o-rings and gaskets

Operating Parameters

Maximum Temperature
Maximum Differential Pressure @ 20°C
Filtration Efficiency

180°F (82°C) @ 15 psid
75 psid (5.2 bard)
Nominal 90%

Recommended Water Flow Rates

0.5 – 5 micron
10 – 50 micron

2.0 gpm/10" length (7.6 lpm/10" length)
5.0 gpm/10" length (18.9 lpm/10" length)

Sanitizing Agents

Chlorine or hydrogen peroxide


ORDERING INFORMATION

Catalog Number and Description

FCDP	All polypropylene depth filter cartridge
X	Cartridge Code: 0 = 2-222 o-rings 7 = 2-226 o-rings w/spear 1 = single open end w/internal o-ring F = double open end w/flat gasket seal
XX	Length (in): 09 = 9.75, 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX	Micron Rating: S5 = 0.5 μm, 01 = 1 μm, 03 = 3 μm, 05 = 5 μm, 10 = 10 μm, 25 = 25 μm, 50 = 50 μm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.

FLOW RATE vs. INITIAL CLEAN PRESSURE DROP





Media Grade	Nominal	99.9% Abs
S5	.5	1
1	1	3
3	3	5
5	5	10
10	10	20
25	25	40
50	50	70



NT Series Graded Pore Polypropylene Depth Filter Cartridge



- Designed to deliver precision prefiltration through the patented advanced melt blown structure that incorporates large diameter fibers for strength while maintaining small fibers for filtration
- High purity, 100% polypropylene construction is free of surfactants, binders and adhesives
- FDA Listed Materials - Manufactured from materials listed for food contact applications in Title 21 of the U.S. Code of Federal Regulations. Product (3 micron and higher) in compliance with EU Directive 2002/72/EC for plastic in food contact (in simulants A, B, C, and D).
- Toxicity - All polypropylene components meet the specifications for biological safety as per the USP for Class VI-121°C plastics (gaskets/O-rings excluded).



SPECIFICATIONS

Dimensions

Diameter (OD).....
Length (in).....

2.5" (6.5 cm)
9.75, 10, 20, 30, 40

Materials

Cartridge.....
Media.....
Seals.....

Polypropylene caps and core
CoLD® fiber melt blown polypropylene
Silicone o-rings and Santoprene® gaskets

Operating Parameters

Maximum Temperature
0.5-10 µm:.....

15-120 µm:.....

15 psid (1.03 bard) @ 180°F (82°C)
25 psid (1.72 bard) @ 150°F (66°C)
60 psid (4.14 bard) @ 86°F (30°C)
25 psid (1.72 bard) @ 140°F (60°C)
50 psid (3.45 bard) @ ambient
60 psi (4.1 bar)

Maximum Differential Pressure @ 30°C
Filtration Efficiency.....

Nominal 90%

Recommended Water Flow Rates

0.5 – 3 micron.....
5 – 75 micron.....

2.0 gpm/10" length (7.6 lpm/10" length)
5.0 gpm/10" length (18.9 lpm/10" length)

Sanitizing Agents.....

Chlorine, hydrogen peroxide

Autoclaving:

Single open end FCNT Series filter cartridges can be autoclaved for 30 minutes at 250°F (121°C) under no end load conditions. However, filter cartridges should be allowed to cool to normal system operating temperatures prior to use.

Steam Sterilization:

Not recommended.

ORDERING INFORMATION

Catalog Number and Description

FCNT	Polypropylene CoLD® depth filter cartridge
X	Cartridge Code: 0 = 2-222 o-rings 7 = 2-226 o-ring locking tabs w/spear 1 = single open end w/internal o-ring N = double open end (0.5 – 5 mm – no gasket)
XX	Length (in): 09 = 9.75, 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX	Micron Rating: S5 = 0.5 µm, 01 = 1 µm, 03 = 3 µm, 05 = 5 µm, 10 = 10 µm, 15 = 15 µm, 20 = 20 µm, 30 = 30 µm, 40 = 40 µm, 50 = 50 µm, 75 = 75 µm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.



Postpure PP™ Graded Density Pleated Polypropylene Depth Media Filter Cartridge

- Composed of graded-density, pleated, polypropylene depth media for high efficiency postfiltration of DI resin applications
- FDA Listed Materials - Manufactured from materials which are FDA listed for food contact applications in Title 21 of the U.S. Code of Federal Regulations.
- Toxicity - All polypropylene components meet the specifications for biological safety as per the USP for Class VI-121 °C plastics (gaskets/O-rings excluded).
- Cartridges are free of resins, binders and adhesives.

SPECIFICATIONS

Dimensions

Diameter (OD) 2.6" (6.6 cm)
 Length (in) 10, 20, 30

Materials

Cartridge Polypropylene caps, core and cage
 Media Pleated, non-woven melt blown polypropylene
 Seals Silicone o-rings and gaskets

Operating Parameters

Maximum Temperature 150°F (65°C) @ 40 psid (2.8 bard)
 Maximum Differential Pressure @ 20°C 75 psid (5.1 bard)
 Filtration Efficiency nominal 90%

Recommended Water Flow Rates


0.3 – 1 micron 2.0 gpm/10" length (7.6 lpm/10" length)
 3 – 30 micron 8.0 gpm/10" length (30.1 lpm/10" length)

Sanitizing Agents

Chlorine, hydrogen peroxide, in-line with hot water (82°C) for one hour, autoclaved for 20 minutes at 121°C under no load conditions.

Sterilization

Multiple autoclaving for 30 minutes at 250°F (121°C) under no end load conditions. In-line steam sterilization is not recommended. May be in-line sanitized with hot water at 180°F (82°C) for 1 hour.



ORDERING INFORMATION

Catalog Number and Description



FCPP	All polypropylene, pleated, nominal depth filter cartridge
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 w/spear 7 = 2-226 o-rings locking tabs w/spear 1 = single open end w/internal o-ring F = double open end w/flat gasket seal
XX	Length (in): 10 = 10, 20 = 20, 30 = 30
XX	Micron Rating: S3 = 0.3 μm, S6 = 0.6 μm, O1 = 1 μm, O3 = 3 μm, O5 = 5 μm, O10 = 10 μm, O30 = 30 μm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.

NA Series Absolute Rated Polypropylene Depth Filter Cartridge



- Absolute filtration with sharp particle cutoffs deliver precise removal efficiencies
- Patented melt blown structure provides outstanding retention efficiency, mechanical strength, and long on-stream life
- High purity, 100% polypropylene construction is free of surfactants, binders and adhesives making these cartridges ideal for use in food and beverage applications
- FDA Listed Materials - Manufactured from materials which are listed for food contact applications in Title 21 of the U.S. Code of Federal Regulations. Product (5 micron and higher) in compliance with EU Directive 2002/72/EC for plastic in food contact (in simulants A, B, C, and D).
- Toxicity - All polypropylene components meet the specifications for biological safety as per the USP for Class VI-121 °C plastics (gaskets/O-rings excluded).



SPECIFICATIONS

Dimensions

Diameter (OD)
Length (in)

2.5" (6.5 cm)
9.75, 10, 20, 30, 40

Materials

Cartridge
Media
Seals

Polypropylene caps and core
CoLD® fiber melt blown polypropylene
Silicone o-rings and gaskets

Operating Parameters

Maximum Temperature
0.5-20 μm:

30-120 μm:

15 psid (1.03 bard) @ 180°F (82°C)
25 psid (1.72 bard) @ 150°F (66°C)
60 psid (4.14 bard) @ 86°F (30°C)
25 psid (1.72 bard) @ 140°F (60°C)
50 psid (3.45 bard) @ ambient

Maximum Differential Pressure @ 30°C

60 psi (4.1 bar)

Filtration Efficiency

Absolute (> 99.9% Retention Rating by ASTM F-795 Test)

Recommended Water Flow Rates

0.5 – 5 micron
10 – 70 micron

2.0 gpm/10" length (7.6 lpm/10" length)
5.0 gpm/10" length (18.9 lpm/10" length)

Sanitizing Agents

Chlorine, hydrogen peroxide

Autoclaving

Single open end Nexis® Series filter cartridges can be autoclaved for 30 minutes at 250°F (121°C) under no end load conditions. However, filter cartridges should be allowed to cool to normal system operating temperatures prior to use.

Steam Sterilization

Not recommended

ORDERING INFORMATION

Catalog Number and Description

FCNA	Absolute rated CoLD depth filter cartridge
X	Cartridge Code: 0 = 2-222 o-rings 7 = 2-226 o-rings w/spear 1 = single open end w/ internal o-ring F = double open end w/flat gasket seal 5 = 2-222 o-rings w/spear
XX	Length (in): 09 = 9.75, 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX	Micron Rating: S5 = 0.5 μm, 01 = 1 μm, 03 = 3 μm, 05 = 5 μm, 10 = 10 μm, 15 = 15 μm, 20 = 20 μm, 30 = 30 μm, 50 = 50 μm, 70 = 70 μm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.



WN Series Pleated Polysulfone Membrane Filter Cartridge

- Composed of pleated highly asymmetric polysulfone membrane over a non-woven polypropylene support layer
- For high flow rates and low pressure drops, absolute rated filters are designed for postfiltration in high purity water applications
- High-purity construction materials are factory rinsed with DI water for quick on-stream rinse up with a minimum of throughput
- Meets criteria for USP Class VI Biological tests for plastics, ensuring that no surfactants or coatings interfere with the application
- FDA listed materials - manufactured from materials which are FDA listed for food contact applications in Title 21 of the U.S. code of Federal Regulations

SPECIFICATIONS

Dimensions

Diameter (OD)	2.6" (6.6 cm)
Length (in)	9.75, 10, 20, 30, 40

Materials

Cartridge	Polypropylene caps, core and cage
Media	Single layer asymmetric hydrophilic polysulfone
Seals	Silicone o-rings and gaskets

Operating Parameters


Maximum Temperature	180°F (82°C) @ 50 psid (3.4 bard)
Maximum Differential Pressure @ 20°C	80 psi (5.5 bar)
Filtration Efficiency	Absolute (> 99.9% Retention Rating by Latex Bead Challenge)

Recommended Water Flow Rates

0.05 micron	1.3 gpm/10" length (4.9 lpm/10" length)
0.1 micron	1.7 gpm/10" length (6.4 lpm/10" length)
0.2 micron	3.0 gpm/10" length (11.3 lpm/10" length)
0.45 micron	5.5 gpm/10" length (20.8 lpm/10" length)

Sanitizing Agents

.....	5% Chlorine, 3% hydrogen peroxide
-------	-------	-----------------------------------



ORDERING INFORMATION

Catalog Number and Description


FCWN	Filter cartridge single layer polysulfone
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear 1 = single open end w/ internal o-ring 7 = 2-226 o-rings w/locking tabs/spear end F = double open end w/flat gasket seal
XX	Length (in): 09 = 9.75, 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX(X)	Micron Rating: S05 = 0.05 μm, S1 = 0.1 μm, S2 = 0.2 μm, S4 = 0.45 μm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it.
 Note: Not all part number combinations are available; consult Technical Support for assistance.

WE Series Pleated Polysulfone Membrane Filter Cartridge



- Composed of a double layer of integrity testable, highly asymmetric polysulfone membrane. These absolute rated filters offers superior bacteria and particle removal for high efficiency postfiltration for critical high purity water applications
- Long on stream life, high flow rates and low pressure drops result from the membrane asymmetry
- High-purity construction materials are factory flushed with DI water for quick on-stream rinse-up with a minimum of throughput
- All polypropylene hardware and thermal welding minimizes extractables
- All materials are FDA listed for contact with food and beverages



(Rinse in @ 5-6 gpm per 10" to ensure removal of air and microbubbles between the membrane layers, especially with 0.02μ. Recommend flow per 10" is 2 gpm.)

SPECIFICATIONS

Dimensions

Diameter (OD)
 Length (in)

Materials

Cartridge
 Media polysulfone
 Seals

Operating Parameters

Maximum Operating Temperature
 Maximum Forward Differential Pressure
 Filtration Efficiency

Sanitizing Agents

Integrity Test

Pore Size

Diffusional Flow Values (100% H₂O) (cc/min) @ Test pressure per 10" length

0.02 μm
 0.1 μm
 0.2 μm
 0.45 μm

2.6" (6.6 cm)
 9.75, 10, 20, 30, 40

Polypropylene caps, core and cage
 Double layer asymmetric hydrophilic

Silicone o-rings and gaskets

86°F / 30°C (158°F / 70°C)

80 psid @ 68°F / 5.5 bar @ 20°C
 20 psid @ 158°F / 1.4 bar @ 70°C
 99.9% Absolute

5% Chlorine or 3% hydrogen peroxide

Diffusional Flow (cc/min) @ Test Pressure per 10" length

< 30 cm³/min @ 50 psig / 3.4 bar
 < 24 cm³/min @ 25 psig / 1.7 bar
 < 20 cm³/min @ 20 psig / 1.4 bar
 < 15 cm³/min @ 15 psig / 1.0 bar

ORDERING INFORMATION

Catalog Number:

FCWE	Filter cartridge double layer polysulfone
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear 1 = single open end w/ internal o-rings 7 = 2-226 o-rings w/locking tabs/spear end F = double open end w/flat gasket seal
XX	Length (in): 09 = 9.75, 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX(X)	Micron Rating: S02 = 0.02 μm, S1 = 0.1 μm, S2 = 0.2 μm, S4 = 0.45 μm

Note: Not all part number combinations are available; consult Technical Support for assistance. To determine your catalog order number, replace the X with one of the numbered/lettered options beside it.



DI Series Pleated Hydrophilic PVDF Media Pharmaceutical/Biotech Grade Filter Cartridge

- Composed of a validatable, hydrophilic, PVDF membrane. Offering a high velocity DI water flush for quick rinse-up with no downstream contamination.
- These absolute rated filters offer superior bacteria and particle removal for critical high purity postfiltration applications
- Filters have single PVDF membrane with two layers of polypropylene support media to ensure absolute bacteria retention with typical LRV >8
- The all PVDF membrane can be sanitized with chlorine, hydrogen peroxide or steam
- Virgin polypropylene construction with fusion welding minimizes extractables
- Cartridges are 100% integrity tested to verify absolute sub-micron particle retention

SPECIFICATIONS

Dimensions

Diameter (OD)	2.75" (7.0 cm)
Length (in)	10, 20, 30, 40

Materials

Cartridge	Polypropylene caps, core and cage
Media	Hydrophilic PVDF
Seals	Silicone o-rings and gaskets

Operating Parameters

Maximum Temperature	176°F (80°C) @ 25 psid (1.7 bar)
Maximum Differential Pressure @ 25°C ..	50 psi (3.4 bar)
Filtration Rating	100% Absolute

Recommended Water Flow Rates

0.1 micron	0.5 gpm/10" length (1.9 lpm/10" length)
0.2 micron	1.0 gpm/10" length (3.8 lpm/10" length)

Sanitizing Agents


Chlorine, hydrogen peroxide

Sterilization

30 SIP cycles of 30 min @ 121°C; 30 autoclave cycles of 60 min @ 121°C

Integrity Test

Pore Size	Minimum Water Bubble Point @ 23°C	Diffusional Flow (cc/min) @ Test Pressure per 10" length in water
0.1 μm	≥ 70 psig (≥ 4.8 bar)	≤ 20 @ 56 psig (3.8 bar)
0.2 μm	≥ 45 psig (≥ 3.1 bar)	≤ 13.3 @ 40 psig (2.8 bar)



ORDERING INFORMATION

Catalog Number and Description

FCDI	Filter cartridge Water DI
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear 7 = 2-226 o-rings w/locking tabs/spear end F = double open end w/flat gasket seal
XX	Length (in): 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX	Micron Rating: S1 = 0.1 μm, S2 = 0.2 μm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.

PV Series Pleated Hydrophilic PVDF Media Pharmaceutical Grade Filter Cartridge



- Cartridge is a validated, pleated hydrophilic PVDF membrane over a non-woven polypropylene support layer
- Code 0, Code 5, and Code 7 configurations are available in 10, 20, 30, and 40-in lengths that are 100% tested in manufacturing to ensure absolute bacteria retention with typical titre reduction of $>10^7/cm^2$
- Quantitative retention of 10^7 CFU/cm² Brevundimonas diminuta ATCC® 19146 per ASTM methodology
- Component materials meet the criteria of the USP <88> Reactivity Test for Class VI Plastics. These products meet the requirements of the USP <88> Safety Test, utilizing a 0.9% sodium chloride extraction
- Component materials meet the “non-fiber releasing” criteria as defined in 21 CFR 210.3 (b) (6)
- Will meet the USP Oxidizable Substances Test requirements after a water flush of ≤ 1 L

SPECIFICATIONS

Dimensions

Diameter (OD) 2.75" (7.0 cm)
 Length (in) 10, 20, 30, 40

Materials

Cartridge Polypropylene caps, core and cage
 Media PVDF
 Seals Silicone o-rings

Operating Parameters

Maximum Temperature 176°F (80°C) @ 25 psid (1.7 bar)
 Maximum Differential Pressure @ 25°C 80 psi (5.5 bar)
 Filtration Rating 100% Absolute
 Toxicity Non-toxic by USP Class VI biological test for plastics
 Validation Quantitative Retention of 10^7 CFU/cm² per ASTM methodology

Recommended Water Flow Rates

0.2 μ m 1.0 gpm/10" length (3.8 lpm/10" length)

Sanitizing Agents

. Chlorine, hydrogen peroxide


Sterilization

. 30 SIP cycles of 30 min @ 135°C; 30 autoclave cycles of 60 min @ 126°C

Integrity Test

Pore Size Minimum Water Diffusional Flow (cc/min)
 Bubble Point @ 23°C @ Test Pressure per 10" length
 0.2 μ m ≥ 50 psig (≥ 3.45 bar) ≤ 13.3 @ 40 psig (3.1 bar)

FLOW RATE vs. INITIAL CLEAN PRESSURE DROP



ORDERING INFORMATION

Catalog Number and Description

FCPV	Filter cartridge pharmaceutical/validated
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear end 7 = 2-226 o-rings w/locking tabs/spear end
XX	Length (in): 10 = 10, 20 = 20, 30 = 30
S2	Micron Rating: S2 = 0.2 μ m

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.



VH Series Pleated PES Media Pharmaceutical Grade Filter Cartridge

- Cartridge is a validated, pleated polyethersulphone membrane over a non-woven polyester support layer
- Code 0, Code 5, Code 7 and Code 10 configurations are available in 10, 20 30, and 40-in lengths that are 100% tested in manufacturing to ensure absolute bacteria retention
- Materials conform to the relevant requirements of 21CFR Part 177 and current USP Plastics Class VI-121°C and ISO10993 equivalents
- FCVH Series Sterilizing Grade 0.2 micron filters are validated by bacterial challenge testing to methods specified in ASTM F838-83 (10⁷ organisms/cm² minimum) with typical in-house challenge levels being 10¹¹ per 10 inch module for Brevundimonas diminuta
- Contain no surfactants or coatings to interfere with your application, and the thermo-plastic construction process minimizes extractables.

SPECIFICATIONS

Dimensions

Diameter (OD)
Length (in)

2.75" (7.0 cm)
10, 20, 30, 40

Materials

Cartridge

Polypropylene, core and cage, nylon endcaps with 316LSS insert

Support

Polyester

Media

Polyethersulphone

Seals

Silicone o-rings

Operating Parameters

Maximum Temperature
Maximum Differential Pressure @ 25°C
Filtration Rating
Toxicity
Validation

176°F (80°C) @ 29 psid (2.0 bar)
72 psi (5.0 bar)
100% Absolute
Non-toxic by USP Class VI biological test for plastics
Microbially retentive and validated to ASTM F838-83 methodology

Recommended Water Flow Rates

0.1 µm
0.2 µm
0.45 µm

1.8 gpm/10" length (2.3 lpm/10" length)
2.0 gpm/10" length (7.6 lpm/10" length)
3.0 gpm/10" length (11.4 lpm/10" length)

Sanitizing Agents

Chlorine, hydrogen peroxide, autoclaved for 20 minutes at 121°C under no load conditions.

Sterilization

FCVH cartridges can be repeatedly in-situ steam sterilized or autoclaved up to 130°C (266°F). They can be sanitized with hot water at up to 90°C (194°F) and are compatible with a wide range of chemicals.

Integrity Test

Pore Size	Minimum Water Bubble Point	Diffusional Flow (cc/min) @ Test Pressure per 10" length
0.1 µm	≥ 34.2 psig*	≤ 27 @ 70 psig (4.9 bar)
0.2 µm	≥ 49 psig	≤ 16 @ 40 psig (2.7 bar)
0.45 µm	≥ 36 psig	≤ 16 @ 25 psig (1.7 bar)


* 60/40 IPA water test solution

ORDERING INFORMATION

Catalog Number and Description

FCVH	Filter cartridge pharmaceutical/validated
X	Cartridge Code: 0 = 2-222 o-rings 1 = single open end w/internal o-ring 5 = 2-222 o-rings w/spear end 7 = 2-226 o-rings w/locking tabs/spear end
XX	Length (in): 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX	Micron Rating: S1 = 0.1 µm, S2 = 0.2 µm, S4 = 0.45 µm

FLOW RATE vs. INITIAL CLEAN PRESSURE DROP



To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.

UF Series Hollow Fiber Polysulfone Media Filter Cartridge



- Composed of validatable hollow fiber polysulfone media with polypropylene hardware
- These absolute rated filters offer excellent bacteria, particle and pyrogen removal for critical pharmaceutical and life science applications, at economical costs
- Code 0, Code 5, and Code 7 configurations are available in 10, 20, 30 and 40-in lengths
- Meet current USP Class VI biological test for plastics, with a validation certificate available
- Contain no surfactants or coatings to interfere with your application, and thermo-plastic construction process minimizes extractables
- Hollow fiber construction ensures strength, while exhibiting low pressure drop and exceptionally high flow rates
- Multi-tube applications require special housings - contact Technical Support

SPECIFICATIONS

Dimensions

Diameter (OD) 2.9" (7.4 cm)
 Length (in) 10, 20, 30, 40

Materials

Cartridge Polypropylene caps and cage, polyurethane end sealant
 Media Polysulfone fibers
 Seals Silicone o-rings

Operating Parameters

Maximum Temperature 185°F (85°C) @ 10 psid (.7 bar)
 Maximum Differential Pressure 30 psi (2 bar) @ 25°C
 Filtration Rating 100% Absolute
 Toxicity Non-toxic by USP Class VI biological test for plastics
 Validation Diffusive flow test methods


Recommended Water Flow Rates

0.05 micron 2.0 gpm/10" length (7.6 lpm/10" length)
 0.1 and 0.2 micron 3.0 gpm/10" length (11.4 lpm/10" length)

Sanitizing Agents

. Chlorine, hydrogen peroxide, autoclaved for 20 minutes at 121°C under no load conditions

FLOW RATE vs. INITIAL CLEAN PRESSURE DROP



ORDERING INFORMATION

Catalog Number and Description

FCUF	Filter cartridge ultra filter
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear end 1 = single open end w/ internal o-ring 7 = 2-226 o-rings w/locking tabs/spear end
XX	Length (in): 10 = 10, 20 = 20, 30 = 30, 40 = 40
XX(X)	Micron Rating: S05 = 0.05 μm, S1 = 0.1 μm, S2 = 0.2 μm

To determine your catalog order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.



316 Stainless Steel, Single-Tube Filter Housing

For Code F

This single-tube cartridge filter housing is made of cast 316 stainless steel and includes 316 stainless steel shell. Housings are available to accommodate 10, 20 or 30-in Code F filter cartridges. The inlet and outlet are 3/4" NPT, and the bowl of each housing is fitted with a 1/4" NPT drain plug. This cartridge filter housing is ideal for a wide variety of low flow applications requiring a high quality prefilter housing or for applications where an industrial pre-filter is used.

- Single tube housings accommodate 10", 20" and 30" Code F filter cartridges
- Housing uses 316SS for construction of the head, bowl and port plug
- Inlet and outlet connections are made to the housing head, allowing cartridges to be replaced without disconnecting the inlet/outlet piping
- Housing can be autoclaved or hot-water sanitized with the cartridges in place for your convenience

SPECIFICATIONS

Dimensions

10-in Housing.....	
20-in Housing.....	
30-in Housing.....	

Length (A)	Width (B)
13.5" (34.3 cm)	4.75 (12.1 cm)
23.5" (59.7 cm)	4.75 (12.1 cm)
33.5" (85.1 cm)	4.75 (12.1 cm)

Materials

Bowl and Head	
Port Plugs	
O-ring	

316 stainless steel
316 stainless steel
Ethylene Propylene

Operating Parameters

Max Operating Pressure	
Max Housing Flow Rate	

175 psi (12.1 bar) @ 200°F (93°C)
12 gpm (45.4 lpm)

Note: Housing rating only, safe operating pressure will depend on filter cartridge and gaskets used.

Connections

Inlet/Outlet	
Drain	


3/4" NPT
1/4" NPT

Mounting


Should be mounted by rigid pipe connections or with optional mounting bracket. Allow enough clearance below bottom of housing to allow cartridge to be changed.

Flow Direction

"Inlet" and "Outlet" are cast on the housing head for user convenience.



HOUSING PRESSURE DROP vs. LIQUID FLOW RATE



ORDERING INFORMATION

Catalog Number and Description

ZHDFD1001	10" housing
ZHDFD2001	20" housing
ZHDFD3001	30" housing
ZHDXDB001	Mounting Bracket
B10015866	Shell O-ring EPDM




316L Stainless Steel, Single-Tube Filter Housing

For Code 0

This single-tube cartridge filter housing is made of 316L stainless steel and includes 316 stainless steel port plugs. Housings are available to accommodate 10, 20 or 30-in Code 0 filter cartridges. The inlet and outlet are 3/4" NPT, and the bowl of each housing is fitted with a 1/4" NPT drain plug. This cartridge filter housing is ideal for a wide variety of low flow applications requiring a high quality prefilter housing or for applications where an industrial pre-filter is used.

- Inlet and outlet connections are made to the housing head, allowing cartridges to be replaced without disconnecting the inlet/outlet piping
- Bowl incorporates a satin finish to help prevent bacterial build-up
- Housing can be autoclaved or hot-water sanitized with the cartridges in place for your convenience
- Two vent ports are included in the head for venting, or for the installation of pressure gauges



SYSTEM SPECIFICATIONS

Dimensions

10-in Housing	14.8" (37.5 cm)	4.2 (10.5 cm)
20-in Housing	24.8" (62.9 cm)	4.2 (10.5 cm)
30-in Housing	34.8" (88.4 cm)	4.2 (10.5 cm)

Length (A)	Width (B)
14.8" (37.5 cm)	4.2 (10.5 cm)
24.8" (62.9 cm)	4.2 (10.5 cm)
34.8" (88.4 cm)	4.2 (10.5 cm)

Materials

Head	316L stainless steel
Bowl and Plugs	316 stainless steel
O-ring	EPDM

316L stainless steel
316 stainless steel
EPDM

Surface Finish

Head	Sand Blasted Finish
Cartridge Sealing Surface	32 RMS Finish
Bowl	Satin Finish

Sand Blasted Finish
32 RMS Finish
Satin Finish

Operating Parameters

Max Inlet Pressure	175 psi (12.1 bar) @ 150°F(66°C)
--------------------	----------------------------------

175 psi (12.1 bar) @ 150°F(66°C)

Note: Housing rating only, safe operating pressure will depend on filter cartridge and gaskets used.

Connections

Inlet/Outlet	3/4" NPT
Drain and Vent	1/4" NPT

3/4" NPT
1/4" NPT

Mounting

Should be mounted by rigid pipe connections or optional mounting bracket. Allow enough clearance below bottom of housing to allow cartridge to be changed.

Flow Direction


"Inlet" and "Outlet" are electroetched on the housing head for user convenience.

ORDERING INFORMATION

Catalog Number and Description

ZHD0D1001	10" housing
ZHD0D2001	20" housing
ZHD0D3001	30" housing
ZHDXDB001	Mounting Bracket
B10015866	Shell O-ring EPDM

HOUSING PRESSURE DROP vs. LIQUID FLOW RATE





316L Electropolished Stainless Steel, Multi-Tube Filter Housing

For Code 5 or Code 0

This multi-tube cartridge filter housing is made of electropolished 316L stainless steel. Housings are available to accommodate 7 cartridges in 10, 20, 30 or 40" length, Code 5 or Code 0 configurations with two 222 o-rings. The bottom of each housing is fitted with a 3/4" NPTF drain plug. And each housing is equipped with a NPTF vent at the top of the housing. A V-band clamp closure allows cartridges to be changed quickly and easily.

- Housing uses electropolished 316L stainless steel construction that is easy to clean and provides maximum corrosion resistance
- Predrilled support stand allows the housing to be secured to floor or some mounting surface
- A 1/4" NPTF air vent plug on the cover allows venting before start-up

FILTER HOUSING SPECIFICATIONS

Dimensions (inches (cm))	Inlet/Outlet	Housing Dimensions				Flange Option E	Max. Flow Rate*/gpm (lpm)
		A	B	C	D		
7-round 10"	2" NPTM (5.1)	25 (64)	11.5 (29)	5.5 (14)	12 (30)	12.8" (32)	35 (132)
7-round 20"	2" NPTM (5.1)	33.5 (85)	11.5 (29)	5.5 (14)	12 (30)	12.8" (32)	70 (264)
7-round 30"	2" NPTM (5.1)	44 (112)	11.5 (29)	5.5 (14)	12 (30)	12.8" (32)	105 (398)
7-round 40"	2" NPTM (5.1)	54.5 (138)	11.5 (29)	5.5 (14)	12 (30)	12.8" (32)	140 (530)

Materials

Head and Shell 316L Stainless Steel electropolished
 Vent and Drain Plug 316 Stainless Steel
 Seat Cups 316L Stainless Steel
 O-Ring Ethylene Propylene



Operating Parameters

Maximum Operating Pressure 150 psi (10.3 bar) @ 200°F (93°C)
 Maximum Water Flow Rate* 140 gpm (528 Lpm)


*Housing rating only, cartridge length and type will effect maximum flow rates

ORDERING INFORMATION

Catalog Number	Description	Inlet/Outlet
ZHH000710	7-round 10"	2" NPTM
ZHH000720	7-round 20"	2" NPTM
ZHH000730	7-round 30"	2" NPTM
ZHH000740	7-round 40"	2" NPTM
ZHH000710F	7-round 10"	2" flange
ZHH000720F	7-round 20"	2" flange
ZHH000730F	7-round 30"	2" flange
ZHH000740F	7-round 40"	2" flange
B10016248	Spare Housing O-Ring EPDM	



FLOW RATE vs. INITIAL CLEAN PRESSURE DROP




316L Stainless Steel, Multi-Tube High Purity Housing


For Code 0 and Code 5, option for Code 7

This multi-tube cartridge filter housing is made of 316L stainless steel, and suited to high purity and sanitary applications. These housings include options to accommodate Code 0 and 5 or Code 7 filter cartridges.

- High quality, crevice free construction
- External mirror polished, internally polished to 32 Ra–EP option
- Steam sterilizable
- Sanitary Tri-Clamp, vent and drain connections
- Band clamp or Rathmann style screw clamp (used on 12, 18, 24 and 30 round vessels) body closure as standard for additional security
- Inlet/outlet available with Tri-Clamp (below) or ANSI flange connections
- Available in Code 0 and 5 (below) or optional Code 7 end cap configuration



ZHHP 3/5/8 Round



ZHHP 12 Round

PRODUCT SPECIFICATIONS

Head and Shell	316L Stainless Steel
Seals	Silicone
Surface Finish	Internal: mechanical polish 32Ra External: mechanical polish, EP option
Cartridge Configuration	Code 0 and 5, Code 7 option
Maximum Operating Pressure	3–8 Round: 145 psig @ 104°F 12 Round: 130.5 psig @ 104°F
Maximum Operating Temperature	3–8 Round: 302°F @ 108.75 psig 12 Round: 302°F @ 101.50 psig

ORDERING INFORMATION

Part Number	Cartridge No.	Cartridge Length	A (in) Dia.	B (in) X-port	C (in) Pipe Dia.	D (in) Overall Height	E (in) Required Clearance	Total Volume (L)	Total Net Weight (kg)
ZHHPON0320T	3	20	6.6	14.2	1-1/2"	41.3	21.3	12.6	19.4
ZHHPON0330T	3	30	6.6	14.2	1-1/2"	51.2	31.1	17.8	21.4
ZHHPON0520T	5	20	8.6	16.5	2"	41.3	21.3	20	20
ZHHPON0530T	5	30	8.6	16.5	2"	51.2	31.1	29.1	22
ZHHPON0820T	8	20	10.7	17.6	2"	41.3	21.3	35.5	30
ZHHPON0830T	8	30	10.7	17.6	2"	51.2	31.1	49.7	33
ZHHPON1220T	12	20	13.8	26.9	3"	47.2	21.3	65	14.5
ZHHPON1230T	12	30	13.8	26.9	3"	57.1	31.1	88	19

Vessel Size	Tri-Clamp Size (in)	Flange Size (in)
3 round	1-1/2"	1-1/4"
5 round	2"	1-1/2"
8 round	2"	1-1/2"
12 round	3"	3"




316 Stainless Steel, Multi-Tube Filter Housing

For Code F


This multi-tube cartridge filter housing is made of 316 stainless steel, and is suited for general-purpose industrial and commercial filtration. These housings can accommodate Code F (DOE) or Code O cartridges, and are available with 6, 12, and 21 tubes in 10, 20, 30, 40-inch lengths.

- The 6 round housings are initially setup for Code F filter cartridges. They can only be adapted to Code O SOE with the addition of the loose compression plate p/n B100237452
- The 12 and 21 round vessels are initially setup to accept Code F, Code O or Code 5
- Incorporates a flow baffle, which deflects incoming flow to prevent cartridge erosion
- An air vent on the cover allows venting before start-up
- A swing bolt closure allows quick disassembly for cleaning and cartridge replacement

6-ROUND DIMENSIONS



12- AND 21-ROUND DIMENSIONS



316 Stainless Steel, Multi-Tube Filter Housing

FILTER HOUSING SPECIFICATIONS

Dimensions (inches (cm))	Inlet/Outlet	Housing Dimensions				Flange Option E	Max. Flow Rate*/gpm (lpm)
		A	B	C	D		
6-round 10"	2 NPTM (5.1)	24 (61)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	30 (114)
6-round 20"	2 NPTM (5.1)	34 (86)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	60 (227)
6-round 30"	2 NPTM (5.1)	45 (114)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	90 (340)
6-round 40"	2 NPTM (5.1)	56 (142)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	120 (454)
12-round 30"	3 flange (7.6)	56 (142)	31 (79)	12 (30)	12 (30)	16.4 (42)	180 (680)
12-round 40"	3 flange (7.6)	66 (168)	31 (79)	12 (30)	12 (30)	16.4 (42)	240 (908)
21-round 30"	4 flange (10.16)	57 (145)	31 (79)	12 (30)	16 (41)	20.8 (53)	315 (1190)
21-round 40"	4 flange (10.16)	67 (170)	31 (79)	12 (30)	16 (41)	20.8 (53)	420 (1560)

Materials

Head, Shell, Plugs . . .	316L Stainless Steel
Internals	316 Stainless Steel
Cover O-Ring	EDPM


Maximum Operating Pressure

6-Round	150 psi (10.3 bar) @ 200°F (93°C)
12-Round	150 psi (10.3 bar) @ 200°F (93°C)
21-Round	150 psi (10.3 bar) @ 200°F (93°C)


ORDERING INFORMATION

Catalog Number	Description	Inlet/Outlet
ZHGOF0610	6-round 10"	2" NPT
ZHGOF0620	6-round 20"	2" NPT
ZHGOF0630	6-round 30"	2" NPT
ZHGOF0640	6-round 40"	2" NPT
ZHGOF0610F	6-round 10"	2" flange
ZHGOF0620F	6-round 20"	2" flange
ZHGOF0630F	6-round 30"	2" flange
ZHGOF0640F	6-round 40"	2" flange
ZHFFI1230	12-round 30"	3" flange
ZHFFI1240	12-round 40"	3" flange
ZHFFI2130	21-round 30"	4" flange
ZHFFI2140	21-round 40"	4" flange
B10020279	Replacement O-ring EPDM - 6-round	
B10015430	Replacement O-ring EPDM - 12-round	

HOUSING PRESSURE DROP vs. LIQUID FLOW RATE



HOUSING PRESSURE DROP vs. LIQUID FLOW RATE



*Housing rating only, cartridge length and type will effect maximum flow rates



304 Stainless Steel, Multi-Tube Filter Housing with V-Clamp Closure

For Code F

This multi-tube cartridge filter housing is made of durable 304 stainless steel, and is suited for general-purpose industrial and commercial filtration. These housings can accommodate Code F (DOE, internals provided), and can be configured for Code 0 and Code 5 cartridges.

- Incorporates a flow baffle, which deflects incoming flow to prevent cartridge erosion
- A 1/4" NPT air vent on the cover allows venting before start-up
- A 3/4" NPT drain plug allows for liquid removal
- Cartridges are independently sealed inside the housing and a single V-band clamp housing closure allows easy cartridge replacement
- Cartridge post can be lifted out, allowing easy removal of cartridges at the bottom of the stack

FILTER HOUSING SPECIFICATIONS

Cartridge Housing	Inlet/Outlet Inches (cm)	Housing Dimensions/Inches (cm)				Flange Opt. E	Max. Flow Rate*/gpm (lpm)
		A	B	C	D		
5-round 10"	1-1/2 NPTM (3.8)	25 (64)	11.5 (29)	5.5 (14)	12 (30)	12.75 (32)	25 (94.6)
5-round 20"	1-1/2 NPTM (3.8)	32.5 (85)	11.5 (29)	5.5 (14)	12 (30)	12.75 (32)	50 (189)
5-round 30"	2 NPTM (5.1)	44 (112)	11.5 (29)	5.5 (14)	12 (30)	12.75 (32)	75 (284)
5-round 40"	2 NPTM (5.1)	54.5 (138)	11.5 (29)	5.5 (14)	12 (30)	12.75 (32)	100 (378)



Materials

Head, Shell, Plugs	304 Stainless Steel
Internals	316 Stainless Steel
Cover O-Ring	Ethylene Propylene
Hold Down Plate Nut	Polypropylene

Operating Parameters

Maximum Operating Pressure	150 psi (10.7 bar) @ 200°F (93°C)
Maximum Housing Flow Rates*	100 gpm (378 lpm)

*Housing rating only, cartridge length and type will effect maximum flow rates




ORDERING INFORMATION

Catalog Number	Description	Inlet/Outlet
ZHFFI0510	5-round 10"	1-1/2" NPT
ZHFFI0520	5-round 20"	1-1/2" NPT
ZHFFI0530	5-round 30"	2" NPT
ZHFFI0540	5-round 40"	2" NPT
ZHFFI0510F	5-round 10"	1-1/2" Flange
ZHFFI0520F	5-round 20"	1-1/2" Flange
ZHFFI0530F	5-round 30"	2" Flange
ZHFFI0540F	5-round 40"	2" Flange
B10016248	Spare Housing O-Ring EPDM	

**Flange inlet and outlet are also available; add F Suffix to part number

HOUSING PRESSURE DROP vs. LIQUID FLOW RATE



304 Stainless Steel, Multi-Tube Filter Housing with Swing Bolt Closure

For Code F

This multi-tube cartridge filter housing is made of 18 gauge 304 stainless steel. Housings are available to accommodate 6, 10, 20, 30 or 40-in, Code F filter cartridges. The inlet and outlet are 2" NPT. There is a 1/2" NPT drain plug, and a 1/4" NPT vent at the top of the housing. A swing bolt closure allows quick disassembly for cleaning and service. This cartridge filter housing is ideal for a wide variety of high flow applications that require an economical, high quality housing.

- Uses 304 stainless steel construction for maximum corrosion resistance to deliver years of dependable service
- A swing bolt closure allows quick disassembly for cleaning and service
- An air vent plug on the cover allows venting before start-up
- This housing accommodates liquid flow rates up to 180 gpm (681 lpm) with operating pressures to 150 psig (10.3 bar)



FILTER HOUSING SPECIFICATIONS

Cartridge Housing	Housing Dimensions/Inches (cm)				Flange Opt. E	Max. Flow Rate*/gpm (lpm)
	A	B	C	D		
6-round 10"	24 (61)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	30 (114)
6-round 20"	34 (86)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	60 (227)
6-round 30"	45 (114)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	90 (340)
6-round 40"	56 (142)	11.2 (28)	5.2 (13)	10.2 (26)	15 (38)	120 (454)



Materials

Head and Shell	304 Stainless Steel
Vent and Drain Plug	304 Stainless Steel
Seat Cups	316L Stainless Steel
O-Ring	Ethylene Propylene

Operating Parameters


Maximum Operating Pressure	150 psi (10.3 bar) @ 200°F (93°C)
Max Water Flow Rate*	120 gpm (454 Lpm)

*Housing rating only, cartridge length and type will effect maximum flow rates



ORDERING INFORMATION

Catalog Number	Description	Inlet/Outlet
ZHGAF0610	6-round 10"	2" NPT
ZHGAF0620	6-round 20"	2" NPT
ZHGAF0630	6-round 30"	2" NPT
ZHGAF0640	6-round 40"	2" NPT
ZHGAF0610F	6-round 10"	2" flange
ZHGAF0620F	6-round 20"	2" flange
ZHGAF0630F	6-round 30"	2" flange
ZHGAF0640F	6-round 40"	2" flange
B10020279	Spare Housing O-ring	





Polypropylene Plastic Filter Housings

These filter housings are molded from polypropylene, and are available in 10 and 20 inch lengths. Housings are supplied with 3/4" inlet and outlets in standard flat gasket design for Code F filter cartridges. Heads are available with double cap plug design and Viton® o-rings.

- Durable housings are made from all polypropylene materials
- Housings contain no fillers, colorants, plasticizers, or lubricants
- Housings are autoclavable, ETO sterilizable, and hydrogen peroxide compatible
- Supplied with 3/4" NPT inlet and outlets in standard flat gasket design for Code F filter cartridges

FILTER HOUSING SPECIFICATIONS

Dimensions	3.5" ID, 5 1/8" OD maximum
Materials	polypropylene cap and housing with standard Viton® E-60 o-rings
Maximum Operating Pressure	125 psi (8.6 bar)
Maximum Operating Temperature	100°F (38°C)
Sterilization/Sanitization	
Hydrogen Peroxide	7.5% compatibility; static soak up to 24 hr at ambient temperature
Weight	
10" housing	3 lb (1.4 kg)
20" housing	4.25 lb (1.9 kg)
Housing Compatibility/Cartridge Type	
ZHCFA1001	Code F, 9 3/4"
ZHCFA2001	Code F, 20"

ORDERING INFORMATION

Catalog Number:	ZHC	F	A	XX	XX
System Name	Polypropylene filter housing				
Cartridge Code		F = Code F			
Cartridge Configuration			A = No plugs	10 = 10	
Length				20 = 20	
Number of Tubes					01 = 1 tube

To figure your order number, replace the X with one of the numbered options below it.

ACCESSORIES

Description	Catalog Number
Mounting Bracket	ZHA150060
Wrench	FC150295
O-ring replacement	ZHA151021

White Polypropylene Plastic Filter Housing for Dialysis Filtration Applications

These filter housings are molded from a white colored, high-density polypropylene, and are available in 12 and 20 inch lengths to accommodate 10 and 20 inch Code 0 filter cartridges. Housings are molded in dies that are minutely polished for an ultra-smooth finish to all contact surfaces, thus minimizing the opportunity for bacteria adhesion. Housings are supplied with 3/4" inlet and outlets. Heads are available with double cap plug design and Viton® o-rings.

- Durable housings are made from all polypropylene materials with FDA approved white colorant
- O-rings are molded of FDA approved Viton®
- Available in 222 o-ring design for Code 0 filter cartridges
- Housings are hydrogen peroxide compatible
- Supplied with 3/4" NPT inlet and outlets



FILTER HOUSING SPECIFICATIONS

Dimensions	3.5" ID, 5 1/8" OD maximum
Materials	White colored polypropylene cap and housing with standard Viton® E-60 o-rings
Maximum Operating Pressure	100 psi (6.9 bar)
Maximum Operating Temperature	100° F (35°C)
Sterilization/Sanitization	
Hydrogen Peroxide	7.5% compatibility; static soak up to 24 hr at ambient temperature
Weight	
12" housing	3.5 lb (1.6 kg)
20" housing	4.25 lb (1.9 kg)
Housing Compatibility/Cartridge Type	
ZHW0D1201	Code 0, 10"
ZHW0D2001	Code 0, 20"

ORDERING INFORMATION

Catalog Number:	ZHW	X	X	XX	XX
System Name	White polypropylene filter housing				
Cartridge Code		0 = Code 0			
Housing Configuration			D = Double cap plug	12 = 12	
Length				20 = 20	
Number of Tubes					01 = 1 tube

To figure your order number, replace the X with one of the numbered/lettered options below it.

ACCESSORIES

Description	Catalog Number
Mounting Bracket	ZHA150060
O-ring Viton®	ZHA151117



Natural Polypropylene Plastic Filter Housing

These filter housings are molded from natural, high-density polypropylene, and is available in 10, 12 and 20 inch lengths. Housings are molded in dies that are minutely polished for an ultra-smooth finish to all contact surfaces, thus minimizing the opportunity for bacteria adhesion. Housings are supplied with 3/4" inlet and outlets in standard flat gasket design for Code F filter cartridges, and 222 o-ring design for Code 0 filter cartridges. Heads are available with double cap plug design and Viton® o-rings.

- Durable housings are made from all polypropylene materials (except for o-rings)
- Housings contain no fillers, colorants, plasticizers, or lubricants
- Available in flat gasket design for Code F filter cartridges, and 222 o-ring design for Code 0 filter cartridges
- Housings are autoclavable and hydrogen peroxide compatible
- Supplied with 3/4" NPT inlet and outlets

FILTER HOUSING SPECIFICATIONS

Dimensions	3.5" ID, 5 1/8" OD maximum
Materials	Natural polypropylene cap and housing with standard Viton® E-60 o-rings
Maximum Operating Pressure	100 psi
Maximum Operating Temperature	38° C (100°F)
Sterilization/Sanitization	
Autoclavable	25 min 121-127°C (252-260°F)
Hydrogen Peroxide	7.5% compatibility; static soak up to 24 hr at ambient temperature
Weight	
10" housing	3 lb (1.4 kg)
12" housing	3.5 lb (1.6 kg)
20" housing	4.25 lb (1.9 kg)
Housing Compatibility/Cartridge Type	
ZHA0D1201*	Code 0, 10"
ZHA0D2001	Code 0, 20"
ZHAFD1001	Code F, 9 3/4"
ZHAFD2001	Code F, 20"

*Code 0, 10" cartridge must be used with 12" housing
 *Code 0 cartridge requires 12" housing

ORDERING INFORMATION

Catalog Number:	ZHA	X	X	XX	XX
System Name	Natural polypropylene filter housing	F = Code F			
Cartridge Code		0 = Code 0		10 = 10	
Housing Configuration			D = Double cap plug	12 = 12	
Length				20 = 20	
Number of Tubes					01 = 1 tube

To figure your order number, replace the X with one of the numbered/lettered options below it.
 *Code 0 cartridge requires 12" housing

ACCESSORIES

Description	Catalog Number
Mounting Bracket	ZHA150060
O-ring Viton®	ZHA151117

CLERIFY™ Oil Adsorption Filter Cartridge

- Composed of sheets of modified cellulose material rolled on a central polypropylene support core
- Removes 95% of total hydrocarbons from water in a single pass. The media can adsorb up to 300% of its own weight in oils
- Available in 2.75" and 4.6" diameters and lengths to 40"



CARTRIDGE SPECIFICATIONS

Dimensions

Diameter (OD) 2.75" (7.0 cm) or 4.5" (11.7 cm)
 Length 9.75", 10", 20", 30", 40"

Materials

Media Modified Cellulose
 Core Polypropylene
 Gaskets Buna N

Operating Parameters

Max. Temperature 120° F (50° C)
 Max. Differential Pressure 36 psi (2.5 bar) @ 25°C

Recommended Water Flow Rates

2.75" Diameter 5.0 gpm/10" Length (18.9 lpm/10" Length)
 4.60" Diameter 5.0 gpm/10" Length (18.9 lpm/10" Length)

ORDERING INFORMATION

Catalog Number:	HAC	X	X	XX	X	X
Hydrocarbon Adsorption Cartridge	HAC					
Cartridge Diameter		A = 2.75" B = 4.5"	0 = 2-222 O-Rings F = Double open end w/flat gasket seals	09 = 9.75 10 = 10 20 = 20 30 = 30 40 = 40		
Cartridge Code						
Length (inches)						
Core Material					P = Polypropylene	
Gasket Material						B = Buna N



Hydrophobic PTFE Media Vent Capsule Filter

- Composed of a pleated hydrophobic PTFE filter membrane rated at 0.01 µm absolute for small volume storage tank venting applications
- Convenient threaded inlet, with 1/2" NPTM inlet fitting screws into 1/2" NPTF bulkhead fitting, eliminates the need for a filter housing
- Hydrophobic expanded PTFE membranes are fully validated by bacterial challenge test methods
- Filters feature thermally-bonded polypropylene cage without using adhesives to ensure low extractables
- 100% integrity tested in manufacturing and can be repeatedly autoclaved with steam up to 140°C

CARTRIDGE SPECIFICATIONS

Dimensions

Diameter (OD)
 Length (in)
 Inner Connection

2.48" (5.6 cm)
 5.9 (15 cm)
 1/2" NPTM

Materials

Cartridge
 Media

Polypropylene
 PTFE Membrane

Operating Parameters

Maximum Temperature
 Maximum Differential Pressure @ 80°C (176°F)
 Air Filtration Rating

60°C (140°F)
 65 psig (4.5 bar)
 0.01 µm 100% Absolute


ORDERING INFORMATION

Catalog Number and Description

FCVPTO6S1 Capsule Hydrophobic PTFE Filter

NOTE: These filter cartridges should not be used as a combination air vent/water overflow device.

CARTRIDGE FLOW RATES



EA Series Hydrophobic Polypropylene Media Vent Filter Cartridge



- Composed of a pleated hydrophobic highly asymmetric polysulfone membrane rated at 0.02 μm absolute for sterile air filtration, storage tank venting applications
- Filter components meet current USP Class VI biological test for plastics
- Contain no surfactants or coatings to interfere with your application, and the thermo-plastic construction process minimizes extractables
- Asymmetric single layer membrane ensures strength, while exhibiting low pressure drop and exceptionally high flow rates
- Sterilized by autoclaving

CARTRIDGE SPECIFICATIONS

Dimensions

Diameter (OD) 2.6" (6.6 cm)
 Length (in) 10, 20, 30

Materials

Cartridge Polypropylene caps, core and cage
 Media Hydrophobic asymmetric polysulfone
 Seals Silicone o-rings and gaskets

Operating Parameters

Maximum Temperature Ambient Air
 Maximum Differential Pressure @ 23°C 60 psi (4.1 bar)
 Air Filtration Rating 0.02 μm 100% Absolute
 Toxicity Non-toxic by USP Class VI biological test for plastics

Sanitizing Agents

. Chlorine, hydrogen peroxide or autoclaving


ORDERING INFORMATION

Catalog Number and Description

FCEA	Filter cartridge vent polysulfone
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear end 1 = single open end w/internal o-ring 7 = 2-226 o-rings w/locking tabs/spear end F = double open end w/flat gasket seal
XX	Length (in): 10 = 10, 20 = 20, 30 = 30
S2	Micron Rating: S2 = 0.02 μm (air)

To figure your order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.

NOTE: These filter cartridges should not be used as a combination air vent/water overflow device.





VA Series Hydrophobic PTFE Validated Membrane Vent Filter Cartridge

- Hydrophobic, pleated PTFE membrane rated at 0.2µm absolute for sterile air filtration
- Materials of construction conform to USP Class VI biological tests for plastics
- High surface area and high voids volume combine to offer exceptional flow rates and extended service life
- Fully validated by aerosol and liquid bacterial challenge
- Filters are integrity testable by all methods including Water Intrusion Test
- FCVA Series is fully retentive to aerosolized *Brevundimonas diminuta* (ATCC 19146) bacteria when challenged with a total of 2×10^9 cfu over a 1-hr test at the rated flow of the cartridge.
- Conformance to the requirements for the non-fibre releasing filters as laid down in the U.S. Food and Drug Administration Regulations 12CFR211.72 and 210.3(b), (6).

CARTRIDGE SPECIFICATIONS

Dimensions

Diameter (OD)
Length (in)

2.6
5, 10, 20, 30

Materials

Cartridge
Membrane
Seals

Polypropylene caps, core and cage
Hydrophobic PTFE
Silicone o-rings

Operating Parameters

Maximum Temperature
Maximum Differential Pressure @ 20°C
Air Filtration Rating
Toxicity

50° C
50 psig
0.02 µm Absolute
All components conform to the Biological Safety Standards identified in USP <88> *Biological Reactivity* to Class VI-121°C levels
ASTM F838-83 Liquid Bacterial Challenge
Fully retentive to both Aerosol Bacteria and Phage Challenge

Sanitizing Agents

Sterilization
.

Can be insitu steam sterilized up to 180 times at 142°C
Chlorine, hydrogen peroxide

Integrity Test @ 20°C

Micron Rating
Minimum Bubble Point (psi)
Pressure Decay Test Pressure (psi)
Maximum Diffusional Flow (ml/min)


0.2 µm liquid rating
14.5
11.6
8.5, 18, 36, 54

ORDERING INFORMATION

Catalog Number and Description

FCVA	Filter Cartridge Vent PTFE
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear end 7 = 2-226 o-rings w/locking tabs/spear end
XX	Length (in): 05 = 5, 10 = 10, 20 = 20, 30 = 30
S2	Micron Rating: S2 = 0.2 µm

To figure your order number, replace the X with one of the numbered or lettered options beside it.
NOTE: These filter cartridges should not be used as a combination air vent/water overflow device.
NOTE: Not all part number combinations are available; consult Technical Support for assistance.



VP Series Hydrophobic PTFE Validated Media Vent Filter Cartridge



- Composed of a pleated, hydrophobic, PTFE, Teflon® membrane rated at 0.2 µm absolute for sterile air filtration, storage tank venting applications
- Filter components meet the criteria of the USP Class VI biological test for plastics
- These filters feature minimal pressure loss, long service life due to high void volume, and can be repeatedly steam sterilized or autoclaved
- Bacterial Growththrough - Prevention of bacterial growththrough by Brevundimonas diminuta for at least 21 days @ a challenge level $\geq 1 \times 10^7$ CFU/cm²

CARTRIDGE SPECIFICATIONS

Dimensions

Diameter (OD)	2.6" (6.6 cm)
Length (in)	10, 20, 30

Materials

Cartridge	Polypropylene caps, core and cage
Media	Hydrophobic Teflon® PTFE
Seals	Silicone o-rings and gaskets

Operating Parameters

Maximum Temperature	Ambient Air
Maximum Differential Pressure @ 21°C	..	72 psi (5.0 bar)
Air Filtration Rating	0.2 µm Absolute
Toxicity	Non-toxic by USP Class VI biological test for plastics
Virus Aerosol Retention	Retention of a worst case challenge of the model bacteriophage Φ X-174 was complete at challenge levels at 10 ⁸ to 10 ¹⁰ virus particles at 1400 sL/min (50scfm) after 50 steam sterilization cycles of 30 minutes at 145°C.


Sanitizing Agents

Chlorine, hydrogen peroxide, autoclaved for 20 minutes at 121°C under no load conditions.

Integrity Test

Bubble point @ 23°C	≥ 13 psig (≥ 900 mbar) nitrogen with 60/40% IPA/Water
Nitrogen Diffusion @ 23°C	≥ 45 mL/min @ 690 mbar (10 psig) in 60/40% IPA/Water

AIR FLOW RATES AT NEAR ATMOSPHERIC PRESSURE (VENT APPLICATIONS)



ORDERING INFORMATION

Catalog Number and Description


FCVP	Filter cartridge vent polysulfone
X	Cartridge Code: 0 = 2-222 o-rings 5 = 2-222 o-rings w/spear end 7 = 2-226 o-rings w/locking tabs/spear end
XX	Length (in): 10 = 10, 20 = 20, 30 = 30
S2	Micron Rating: S2 = 0.2 µm

To figure your order number, replace the X with one of the numbered or lettered options beside it. Note: Not all part number combinations are available; consult Technical Support for assistance.

NOTE: These filter cartridges should not be used as a combination air vent/water overflow device.

CDI, DI Gard, Prepure DP, Postpure PP, ROGARD are trademarks of Siemens, its subsidiaries or affiliates.

Santoprene is a trademark of Advanced Elastomer Systems, LP
 ATCC is a trademark of the American Type Culture Collection
 Viton is a trademark of DuPont Performance Elastomers LLC
 Teflon is a trademark of E.I. du Pont de Nemours & Company
 CoLD and Nexis are trademarks of Filterite Corporation
 Clerify is a trademark of Pentair Filtration, Inc.



Siemens Water Technologies North America Service Network

For further information, visit:
www.siemens.com/water or contact:

Siemens
Water Technologies

North America and Canada
800.875.7873 ext. 5000 *Technical Support*
800.466.7873 *Customer Service*
tech.support.water@siemens.com

Information Desk
800.525.0658 *Toll Free*
+724.772.1402 *International*
information.water@siemens.com

The information provided in this brochure contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

AFT-CART-BR-009
Subject to change without prior notice.

© 2009 Siemens Water Technologies Corp.