


TYPICAL DESIGN

MATERIAL: 316 SS
 END CONNECTIONS CAN BE
 MODIFIED TO SUIT.



DESIGN SPECIFICATIONS:

FLOW RATE	-----2 MINIMUM
(GPM)	5 CONTINUOUS
	7 INTERMITTENT
RESIN VOLUME	-----1.5 CU.FT.
BED AREA	-----0.6 SQ.FT.
DESIGN PRESSURE	-----125 PSIG CODE
TEMPERATURE	-----100°F
WEIGHT	-----150 SHIPPING
(LBS)	300 OPERATING

PERMUTIT POWER PRODUCTS
 XP-10 NON-REGENERABLE
 DEMINERALIZER



IP&S
 BRIDGEWATER N.J.
 (908) 704-9027