

Water Champ® Chemical Induction Unit 4" Submersible F Series Model No. SWC3F

General Description

The Water Champ® Submersible Chemical Induction System is an innovative device designed for the application of a variety of chemicals used for the treatment of potable water and wastewater. The unique feature of the Water Champ® System is its ability to provide instantaneous mixing and diffusion.

The "F" Series submersible offers the highest quality of design and construction of any submersible chemical induction unit. The hermetically sealed 316 SS motor offers the highest level of durability and performance required for chemical feed applications. Most wetted materials are constructed from Grade 2 Titanium (unalloyed) and are designed for use with most treatment chemicals. The innovative mounting is configured for mounting in open-channel applications and can be easily retrofitted to existing basins and tanks.

Features

- Titanium wetted parts*
- Rugged construction
- Heavy duty bearing design

Key Benefits

- Instantaneous diffusion and mixing
- Energy and chemical savings
- Maximum chemical concentration with no off-gassing
- Warranty - 1 year from start-up or 18 months after delivery whichever occurs first

Specifications


| Model No. | KW (HP) | Max. Gas Induction CL ² kg/d (ppd) | Max. Liquid Induction lpm US gpm | Max. Vacuum kPa (in Hg) |
|-----------|---------|---|----------------------------------|-------------------------|
| SWC3F | 2.2 (3) | 680.3 (1,500**) | 56.8 (15**) | .61 (18) |

* Custom materials quoted upon request.

** Feed rates are application dependent (consult factory).



Typical Water Champ® System Horizontal Installation



| Materials of Construction | |
|---------------------------|-----------------------------|
| Part | Material |
| Vacuum Chamber | Titanium |
| Vacuum Port | Titanium |
| Vacuum Enhancer | Non-Metallic |
| Propeller | Titanium |
| Propeller Bolt | Titanium |
| Shaft | Titanium |
| Mechanical Seals | Carbon / Ceramic |
| Motor | 316 Stainless Steel |
| Power Cable | TC Type (25 ft standard) |
| Hardware | 316 Stainless Steel |

| Motor Performance Data | | | | | | | | | | | | | | | | |
|------------------------|------------|-------|-------|-------|------|------------|------|-------------------------------|------------------------------|-------------------------|----------------|------|------|--------------|------|------|
| Model | KW (HP) | Volts | Phase | Hertz | RPM | Insulation | S.F. | FLA Rated Input Amps | SFA Max. Input Amps | Locked Rotor Amps | Power Factor % | | | Efficiency % | | |
| | | | | | | | | | | | S.F. | F.L. | 3/4 | S.F. | F.L. | 3/4 |
| SWC3F | 3.7 (3) | 200 | 3 | 60 | 3450 | Class B | 1.15 | 10.9 | 12.5 | 71 | 81.5 | 77.8 | 69.5 | 75.5 | 75.2 | 73.2 |
| SWC3F | 3.7 (3) | 230 | 3 | 60 | 3450 | Class B | 1.15 | 9.5 | 10.9 | 62 | 81.5 | 77.8 | 69.5 | 75.5 | 75.2 | 73.2 |
| SWC3F | 3.7 (3) | 230 | 1 | 60 | 3450 | Class B | 1.15 | Y 14 B 12.2 R 4.7 | Y 17 B 14.5 R 4.5 | 82 | 98 | 97.5 | 96 | 70.9 | 71.8 | 69.6 |
| SWC3F | 3.7 (3) | 460 | 3 | 60 | 3450 | Class B | 1.15 | 4.8 | 5.5 | 31 | 81.5 | 77.8 | 96.5 | 75.5 | 75.2 | 73.2 |
| SWC3F | 3.7 (3) | 575 | 3 | 60 | 3450 | Class B | 1.15 | 6.4 | 7.1 | 25 | 81.5 | 77.8 | 69.5 | 75.5 | 75.2 | 73.2 |

Siemens
Water Technologies

Germany
+49 8221 9040
wtger.water@siemens.com

United Kingdom
+44 1732 771777
wtuk.water@siemens.com

USA
+1 800 809 0971
stranco.water@siemens.com

© 2008 Siemens Water Technologies Corp.
Literature No.: ST.070.311.S03.IE.PS.1208
Subject to change without prior notice.

Water Champ is a trademark of Siemens, its subsidiaries or affiliates.

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of the contract.