

# PolyBlend® Polymer Feed System M-Lo Series

The PolyBlend® M-Lo Series polymer feed system offers all of the benefits of the best available polymer preparation technology at a new competitive price. The ready-to-install system provides consistent and accurate dosage and improves polymer efficiency.

The PolyBlend® M-Lo System is engineered for easy installation and maintenance. The compact size of the feeder allows trouble-free installation in confined spaces and the open-frame design facilitates easy component access.

The REM-1E controller is included to provide speed control for the neat polymer pump. The easy to read LCD display indicates strokes per minute (SPM) or strokes per hour (SPH). The microprocessorbased controller is housed in a NEMA 4X enclosure.

The PolyBlend® M-Lo Series polymer feed system is available in several models. The versatility of the PolyBlend® M-Lo System provides a choice of wide range of dosage rates. Multiple configurations offer the flexibility for most polymer feed applications.

## Specifications

Power	115 VAC / 60 Hz / 1 Phase / 10A
Dimensions (W x H x D)	685.8 x 673.1 x 228.6 mm 27" x 26.5" x 9"
Polymer pump	Electronic Metering
Material	304 SS Frame / PVC
Controls	Microprocessor-based REM-1E
Connections	Water In: 12.7 mm (F) NPT (1/2") Discharge: 19.05 mm (F)NPT (3/4") Polymer: 12.7 mm (F)NPT (1/2")

## Key Benefits

- Improved polymer efficiency
- Easy installation & maintenance
- Rugged & reliable design
- Direct drive mix chamber
- Pump interchangeability
- Simple electronic controls
- Competitive price




## Product Sheet

## Model Selection

Model	Pump Output		Flowmeter Range		Polymer Connection (F)NPT		Water Connection		Discharge	
	LPH	GPH	LPH	GPH	mm	in	mm	in	mm	in
M20-0.4	1.5	0.4	11.4 - 83.3	3 - 22	12.7	1/2"	12.7	1/2"	19.1	3/4"
M20-1	3.8	1.0	11.4 - 83.3	3 - 22	12.7	1/2"	12.7	1/2"	19.1	3/4"
M60-0.4	1.5	0.4	22.8 - 227.1	6 - 60	12.7	1/2"	12.7	1/2"	19.1	3/4"
M60-1	3.8	1.0	22.8 - 227.1	6 - 60	12.7	1/2"	12.7	1/2"	19.1	3/4"
M120-0.4	1.5	0.4	45.4 - 454.2	12 - 120	12.7	1/2"	12.7	1/2"	19.1	3/4"
M120-1	3.8	1.0	45.4 - 454.2	12 - 120	12.7	1/2"	12.7	1/2"	19.1	3/4"
M120-2.5	9.5	2.5	45.4 - 454.2	12 - 120	12.7	1/2"	12.7	1/2"	19.1	3/4"

## General Layout



Key Description	
1	Base Assembly
2	Solenoid Valve
3	Priming Port, Pump
4	Differential Pressure Switch
5	Flowmeter
6	Flow Control Valve
7	Digital Display Pump Controller, REM-1E
8	Motor
9	Solenoid Valve
10	Water Inlet
11	Polymer Inlet
12	Mix Chamber Assembly
13	Solution Discharge
14	Pressure Gauge
15	On/Off Main Power Switch
16	Mixer Motor Switch
17	Fuse (Qty 2)
18	Power Cord
19	DP Switch Relay Box

Siemens  
Water Technologies  
  
Germany  
+49 8221 9040  
wtger.water@siemens.com

United Kingdom  
+44 1732 771777  
wtuk.water@siemens.com

USA  
+1 800 245 3006  
dewatering.water@siemens.com

© 2008 Siemens Water Technologies Corp.  
Literature No.: EP.480.330.MLO.IE.PS.1108  
Subject to change without prior notice.

PolyBlend and Hydroforce trademarks of Siemens, its subsidiaries or affiliates. NEMA is a trademark of National Electrical Manufacturers Association. Protected by U.S. Patents 4778280, 5061456, 5164429, 5018871, 5252635, 5316031, 5135968.

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of the contract.