

# Water Champ® Chemical Induction Unit 6" Submersible F Series Model No. SWC5F

## General Description

The Water Champ® Submersible Chemical Induction System is an innovative device designed for the application of a variety of chemicals used for the treatment of potable water and wastewater. The unique feature of the Water Champ® System is its ability to provide instantaneous mixing and diffusion.

The "F" Series submersible offers the highest quality of design and construction of any submersible chemical induction unit. The hermetically sealed 316 SS motor offers the highest level of durability and performance required for chemical feed applications. Most wetted materials are constructed from Grade 2 Titanium (unalloyed) and are designed for use with most treatment chemicals. The innovative mounting is configured for mounting in open-channel applications and can be easily retrofitted to existing basins and tanks.

## Features

- Titanium wetted parts\*
- Rugged construction
- Heavy duty bearing design
- Motor monitoring system

## Key Benefits

- Instantaneous diffusion and mixing
- Energy and chemical savings
- Maximum chemical concentration with no off-gassing
- Warranty - 1 year from start-up or 18 months after delivery whichever occurs first

## Specifications


Model No.	KW (HP)	Max. Gas Induction CL <sup>2</sup> kg/d (ppd)	Max. Liquid Induction lpm US gpm	Max. Vacuum kPa (in Hg)
SWC5F	3.7 (5)	1,360.8 (3,000**)	94.7 (25**)	74.6 (22)

\* Custom materials quoted upon request.

\*\* Feed rates are application dependent (consult factory).



## Typical Water Champ® System Horizontal Installation



### Materials of Construction

Part	Material
Vacuum Chamber	Titanium
Vacuum Port	Titanium
Vacuum Enhancer	Non-Metallic
Propeller	Titanium
Propeller Bolt	Titanium
Shaft	Titanium
Mechanical Seals	Silicone Carbide
Motor	316 Stainless Steel
Power Cable	TC Type (25 ft standard)
Hardware	316 Stainless Steel

### Motor Performance Data

Model	KW (HP)	Volts	Phase	Hertz	RPM	Insulation	S.F.	FLA Rated Input Amps	SFA Max. Input Amps	Locked Rotor Amps	Power Factor %			Efficiency %		
											S.F.	F.L.	3/4	S.F.	F.L.	3/4
SWC5F	3.7 (5)	200	3	60	3450	Class F	1.15	25.1	28.3	150	83	80.5	73.8	79.8	80	78.7
SWC5F	3.7 (5)	230	3	60	3450	Class F	1.15	21.8	24.6	130	83	80.5	73.8	79.8	80	78.7
SWC5F	3.7 (5)	460	3	60	3450	Class F	1.15	10.9	12.3	65	83	80.5	73.8	79.8	80	78.7
SWC5F	3.7 (5)	575	3	60	3450	Class F	1.15	8.7	9.8	52	83	80.5	73.8	79.8	80	78.7
SWC5F	3.7 (5)	230	1	60	3450	Class F	1.15	Y 36.5 B 34.4 R 5.5	Y 42.1 B 40.5 R 5.4	165	91	91	87.2	87.2	74.4	74.2

Siemens  
Water Technologies

Germany  
+49 8221 9040  
wtger.water@siemens.com

United Kingdom  
+44 1732 771777  
wtuk.water@siemens.com

USA  
+1 800 809 0971  
stranco.water@siemens.com

© 2008 Siemens Water Technologies Corp.  
Literature No.: ST.070.312.S05.IE.PS.1208  
Subject to change without prior notice.

Water Champ is a trademark of Siemens, its subsidiaries or affiliates.

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of the contract.