


Strantrol® Controller Accessories Probe-Clean System

12 Gallon Tank Assembly (8801302)

- Natural polyethylene tank, 12 gallon capacity.
- Molded recess for mounting of pump.
- Convenient and light weight, ships economically.
Shipping weight: 3.2 kg (7 lbs.)
- 2" screw-on cap allows a replenishing of chemical solution.
- Slightly translucent, yet rugged design allows checking solution level at a glance.



Data Sheet

Water Technologies

SIEMENS

Technical Data

Output Capacity											
Gallons Per Day		Liters Per Day		Gallons per Hour		Liters per Hour		ML or CC per Minute		Maximum Injection Pressure	
Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Bar	PSI
4.8	24	18.17	90.85	.200	1	.760	3.8	12.67	63	7.6	110

Materials of Construction			
Head	Liquifram	Seal Rings	Connections
PVDF	Fluorofilm®	Polyprel®	.375" Tubing

Voltage	120 VAC, 50/60 Hz, single phase
Peak Input Power	160 watts
Avg. Input Power at Max. Speed	20 watts
Stroke Frequency	100 spm fixed
Stroke Length	Adjustable 0-100% (20% rec.min)
Length	171 mm (7.75") max.
Width	104 mm (4.06") max.
Height	171 mm (6.37") max.

System also includes:
 In-line check valve (9572111)
 Tube connector (2731234)

Siemens
 Water Technologies

Germany
 +49 8221 9040
 wtger.water@siemens.com

United Kingdom
 +44 1732 771777
 wtuk.water@siemens.com

USA
 +1 800 809 0971
 stranco.water@siemens.com

© 2008 Siemens Water Technologies Corp.
 Literature No.: ST.040.860.003.IE.DS.0409
 Subject to change without prior notice.

Strantrol is a trademark of Siemens, its subsidiaries or affiliates. Fluorofilm and Polyprel are trademarks of Milton Roy Company.

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of the contract.