

Wallace & Tiernan® Analyzers/Controllers

SFC SC

Flow proportional control

General

The Wallace & Tiernan® SFC SC system is used for flow proportional controlled dosing of chemicals used in water treatment and for similar industrial process applications. It can control automatic v-notch positioners in gas feed systems, such as the V10k™ and V2000™ systems, or automatic stroke length positioners and variable speed drives in dosing pump systems.

The SFC SC system is available either as stand alone wall-mounted unit, equipment-mounted, or as a panel-mountable unit for installation in a control enclosure.

The SFC SC flow proportional control compliments the SFC series of products which measure and control various parameters, including free and total chlorine, chlorine dioxide, ozone, fluoride, ORP (redox) and pH value.

Typical applications

- Potable water treatment
- Waste water treatment
- Cooling water circuits
- Industrial and process water treatment
- Swimming pools

Features

- Determines the control signal for the positioner/dosing pump from the control variable and the dosing factor
- Sets the position of the positioner accurately using a feedback signal
- Automatic correction in the event of non-linearity of the gas feeder
- Wide dosage range: 10 – 400 %
- Electronic override
- Milliamp or relay output control signals
- Security access

Benefits:


- Easy to operate thanks to intuitive menu navigation, diagnostics menu to simplify maintenance and installation, automatic display of any faults
- Multiple correction values can be used for linearization of the dosing feedback
- Graphical display of all parameters and process variables
- User-selectable units for flow and dosing
- Galvanically isolated inputs and outputs




The intuitive menu structure is controlled via 3 function keys, 4 navigation keys and an escape and acknowledge key.

Product Sheet

SFC electronic module	
Display	Back-lit LCD display, resolution 128 x 64 pixels
Measurement input	0/4 – 20 mA, 47 Ω impedance, isolated
Feedback input	0/4 – 20 mA or 0 – 1 V or 1 kΩ, 5 kΩ potentiometer, linearization over maximum 11 correction values
Digital inputs	2 x inputs for voltage-free contact (< 100 Ω) power supply via SFC SC (12 V)
Switching relay outputs	2 alarm contacts/controller outputs
▪ Switching values	5 A, 250 V AC, 1250 VA max 5 A, 220 V DC, 150 W max
▪ UL/CSA-rating	5 A, 1/6 HP 125, 250 V AC 5 A, 30 V DC, 30 W max 1 A, 30 V DC – 0.24 A, 125 V DC
Analog output	0/4 – 20 mA; load protected ≤ 500 Ω; Accuracy < 0.5 % FS; Galv. isolated up to 50 V relative to earth
Sensitivity	Actuator deadband adjustable from 0.1 to 0.5 % of full scale
Speed of response	Completes a step change in input over full scale within 75 sec
Interface	RS 232 for firmware updates
Characteristics	Dosage factor adjustable from 10 – 400 %; Flow scaling factor free selectable; Sensitivity speed of response
Power supply	24 V DC or 100 – 240 V AC, 50/60 Hz
Ambient temperature	0 – 50 °C (32 – 122 °F)
Enclosure	IP 66, designed to meet NEMA 4X
Installation options	Wall-mounted, equipment-mounted (e.g. V10k, V2000), or panel-mounted in a control enclosure
Weight (incl. packaging)	approx. 2.5 kg (5.5 lbs)
Dimensions (W x H x D)	185 x 265 x 145 mm (7.3 x 10.4 x 5.7 ")
Testing and marking	CE, EMC-EN 61326 LUD-EN 61010 UL listed/CSA certified



Dosing is directly proportional to the measured flow rate.



Siemens
Water Technologies

Germany:
+49 8221 9040
wtger.water@siemens.com

United Kingdom:
+44 1732 771777
wtuk.water@siemens.com

USA:
+1 856 507 9000
wtus.water@siemens.com

© 2008 Siemens Water Technologies
WT.050.590.020.IE.PS.0708
Subject to change without prior notice.

V10k, V2000 and Wallace & Tiernan are trademarks of Siemens, its subsidiaries or affiliates. CSA is a trademark of the Canadian Standards Association. NEMA is a trademark of the National Electrical Manufacturers Association. UL is a trademark of Underwriters Laboratories, Inc.

The information provided in this brochure contains merely general descriptions of characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.