

PV[®] Series Liquid Phase Adsorbers

PV-500, PV-1000, PV-2000

Applications

The PV[®] Series adsorbers are designed for use in a wide range of low/high flow and pressure applications.

- Groundwater remediation
- Wastewater filtration
- Tank rinse water treatment
- Pilot testing
- Underground storage tank clean up
- Leachate treatment
- Dechlorination
- Spill cleanup
- Hydrotesting
- Drinking Water

Installation, Startup and Operation

Siemens can provide a total service package that includes utilizing OSHA trained personnel providing on-site carbon changeouts, packaging and transportation of spent carbon for recycling at our reactivation facilities.



At the time of purchase or rental of the adsorbers, arrangements should be made for the reactivation of the spent carbon. Siemens will provide instructions and assistance on how to obtain acceptance of the spent carbon at our reactivation facilities. Spent carbon cannot be accepted for reactivation until the acceptance process is completed.

Benefits & Design Features


- Durable, carbon steel construction includes internally/externally welded seams.
- SSPC-SP5 sandblasted, NSF-approved baked epoxy interior coating; urethane exterior finish.
- Approved for the transport of hazardous spent carbon.
- Top and side manways permit easy access and inspection of vessels internals and linings.
- Skid-mounted for easy handling and installation.
- Optimized underdrain system for low pressure drop operation.

Piping Manifold (Optional)

- 2"/3" sch 80 PVC piping and valves that allow either adsorber to be used in the lead or lag position (optional carbon steel and stainless steel piping).
- Series or parallel operation.
- Clean utility water connection for manual backflush.
- Sampling ports and pressure gauges.
- Flexible hoses with Kamlock fittings allow easy installation and removal during service exchange operations.
- Available for purchase or rental.

Specification/Typical Properties			
	PV®-500	PV®-1000	PV®-2000
Dimensions (Dia. x Overall Height – Approx.)	30" x 5'7"	48" x 5'7"	48" x 8'8"
Inlet Connection, (Top)	2"	3" NPT (Female)	3" NPT (Female)
Outlet Connection, (Bottom)	2"	3" NPT (Male)	3" NPT (Male)
Manway, Top & Lower Side	11" X 15" (top only)	11" X 15"	11" X 15"
Internal Piping	PVC	PVC	PVC
Interior Coating (All Units)	Epoxy	Epoxy	Epoxy
Exterior Coating (All Units)	Epoxy/Urethane	Epoxy/Urethane	Epoxy/Urethane
Carbon Fill Volume (Cu.ft.)	18.5	34	68
Vessel Weight (lbs.):			
Shipping (With Carbon)	1050	1910	3200
Operating (Approx.)	1750	4300	7500
Flow, GPM (Nominal)	25	50	100
Pressure, PSIG (Maximum) ¹	75	75	75
Temperature °F. (Maximum)	140	140	140
Pounds Of Activated Carbon	500	1000	2000
Contact Time @ Max Flow/Min	5	5	5
Backflush rate (GPM) @ 55°F	15-20	40-50	40-50

¹The PV® Series adsorbers are not ASME code stamped. Pressure rating applies to liquid only. For detailed dimensional information or drawings, contact your local Siemens sales representative. For information on the HP® Series ASME code stamped adsorbers, contact your local Siemens representative.



Safety Note: Wet activated carbon readily adsorbs atmospheric oxygen. Dangerously low oxygen levels may exist in closed vessels or poorly ventilated storage areas. Workers should follow all applicable state and federal safety guidelines for entering oxygen depleted areas.

All information presented herein is believed reliable and in accordance with accepted engineering practices. Siemens makes no warranties as to completeness of information. Users are responsible for evaluating individual product suitability for specific applications. Siemens assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.