

Wallace & Tiernan® Gas Feed Systems

V10k Gas Feeder

SIEMENS

The V10k is a remote vacuum solution feeder for use with four of the most commonly used gases for the disinfection and treatment of municipal and industrial water and wastewater. This unit has been built to continue the long standing proven design and features of its predecessor and adds more. The versatility of wall mounting, front access of all components and maximum capacity of 750 PPD (340 Kgs/day chlorine) have all been enhanced by this new design.

The V10k gas feed system consists of a vacuum regulator mounted at the gas supply, a wall-mounted gas control unit with a rotameter for indication of feed rate and a water-operated injector that provides the vacuum source to drive the entire system. Using automatic switchover regulators, the V10k provides an uninterrupted supply of gas to maintain continuous disinfection/treatment.



KEY BENEFITS:

- Unique, versatile wall-mounted configuration provides for operator convenience and stable control platform
- Integral, automatic switchover to a fresh gas supply insures continuous operation
- Large 5" and 10" flowmeters for the highest degree of readability and accurate indication of feed rate
- Flexible control options from manual to fully automatic systems
- Easily serviced without the need for special tools
- Handles all water treatment gases – chlorine, ammonia, sulfur dioxide, and carbon dioxide



Municipal or Industrial
Water Treatment

- Disinfection of potable water
- Treatment of cooling water to inhibit biological growth and for algae control in irrigation systems



Municipal or Industrial
Waste Treatment

- Disinfection of municipal sewage effluent



Chemical Processing

Treatment of industrial wastes from:

- metal finishing
- pulp and paper operations
- chemical plants
- food processing plant discharges



Industrial Process Water

- Taste and odor control in bottling plants and breweries
- Tempering water treatment and bleaching in flour mills
- High purity water in:
 - electronics
 - pharmaceuticals
 - cosmetic industries



Recreational Pools

- Swimming pool disinfection
- CO₂ feed for pH control

FEATURES

- Versatility – a wall-mounted gas feeder available in a configuration to meet your water treatment requirements.
- Proven V-Notch Flow Control Technology – for accuracy and repeatability.
- Premium Construction – features a one-piece molded headblock for reliability and endurance.
- Large 5" and 10" Rotameters -- available in 14 capacities up to 750 PPD Cl₂ for the highest degree of readability.
- Serviceability – components easily accessible for servicing without tools.
- Flexible Control Modes – manual to fully automatic control schemes.
- Differential-Type Regulation – allows for lower vacuum levels and efficient, economical injector operation.
- Handles All Water Treatment Gases – Chlorine, Ammonia, Sulfur Dioxide and Carbon Dioxide.

APPLICATIONS

- Municipal & Industrial Water & Wastewater treatment
- Treatment of industrial waste from chemical processing
- Industrial Process Water
- Recreational Pools

CONTROL METHODS

Feed rate of any V10k Chlorinator is controlled by either one or both of these methods: interrupting the injector-water supply to shut off the chlorinator's operating vacuum; changing v-notch-orifice area (by positioning the v-grooved plug in its ring) while holding vacuum differential across the orifice constant.

MANUAL CONTROL

Manual control by changing orifice area (v-notch-plug position) via an adjustment knob on the chlorinator.

START-STOP OR PROGRAM CONTROL

This type of control is achieved with simple implementation. A V10k Chlorinator's operating vacuum is started and stopped by interrupting the injector water supply. A solenoid valve or motorized valve is wired into the control circuit of a pump, switch, controller, or timer. Similar to this, a special vacuum line solenoid valve can be used in the gas line to the injector.

AUTOMATIC CONTROL

The V10k can be provided with automatic feed rate control ranging from simple to complex control schemes. The control system can consist of a simple direct mA control V-notch actuator or a more sophisticated control including an actuator and a controller (choice of either an SCU (Signal Conditioning Unit) or a PCU (Process Controller Unit)). Either controller can be remote mounted or on the panel with the V10k.

Direct 4-20 mA input control
(see WT.040.050.000.UA.PS)


- Direct 4-20mA input signal from an external control device.
- Compact integral design
- Internal dosage capability

SCU (see WT.040.100.000.UA.PS)

- Operating Modes: flow proportional, manual
- Inputs: 4-20 mA DC (from flow transmitter)
- Outputs: Control out to actuator; also 4-20 mA output for retransmission of gas feed rate (actuator position)
- Control Capability: Dosage and flow scaling

PCU (see WT.040.200.000.UA.PS)

- Operating Modes: Direct residual feed back, compound loop, feed forward, flow proportional, manual
- Ranges: Setpoints up to 50 mg/L and center-zero capability for dechlorination
- Inputs: Up to 3 analog (flow, residual, spare); 2 digital
- Outputs: Control out to actuator; plus user-configurable 4-20 mA; RS-485 serial communications
- Control Logic: Proportional and integral with lag
- Alarms: Four user-configurable for 16 different conditions



OPERATION

The V10k gas feed system operates under a vacuum that is produced at the injector and transmitted through the control unit to the vacuum regulating valve located at the gas supply. Gas enters the vacuum regulating valve and moves toward the flow control components under a vacuum.

Gas next passes through the rotameter, where its flow rate is measured and the V-Notch orifice, where feed rate is controlled manually or by an automatic positioner. At the injector, the metered gas is dissolved in the water stream. The resultant solution is discharged to the point of application.

1.) VACUUM REGULATORS

Vacuum regulating valves, mounted on the gas supply containers, immediately reduce the pressurized gas to a vacuum. Three capacity regulators are available for both standard and switchover applications: 200 PPD, 500 PPD, and 3000 PPD.

The 200 and 500 PPD regulators feature:

- Positive Indication of Operating Status – A unique lever mechanism and front panel knob provide the operator with a quick indication of 3 or 4 operation modes (operating, low gas supply, off, and standby for automatic switchover arrangements). An additional built-in red indicator becomes visible in the low/out-of-gas situation and an optional contact is available for remote indication.
- Secondary Pressure Check – The 500 PPD regulator has a unique, built-in additional check valve, designed to confine gas under pressure should dirt build up on the primary valve seat.
- Local or Remote Vent Valve – The pressure relief vent is built into the regulator housing to keep all vent lines in the gas supply room.

The standard 3000 PPD regulator arrangement contains a single vacuum regulator and stand-by pressure relief valve. For continuous supply of gas being fed, an automatic switchover version is available that includes a pair of vacuum regulating valves.

2.) ROTAMETER

Large scale, 5" and 10" rotameter tubes provide clear and accurate indication of feed rate, with 13 capacities available in each size (14 for chlorine).

3.) DIFFERENTIAL REGULATING VALVE

Maintains the proper vacuum differential across the V-Notch orifice for consistent feed rate, regardless of changes in operating vacuum.

4.) AUTOMATIC POSITIONER

For automatic control, this positioner moves the V-Notch plug up to 3" (compared to a fraction of an inch for competitive systems) in precise response to the application requirements. Features include:

- NEMA 4X enclosure
- Manual override is achieved by simply pulling the knob to disengage the drive motor.
- Three sets of customer contacts for system interface: Manual Override, MAX position and MIN position.
- Internal feedback potentiometer for precise operation with the SCU or PCU controllers.

5.) VACUUM GAUGE

Provides indication of operating vacuum level. A direct acting diaphragm mechanism eliminates liquid-filled chambers.

6.) INJECTORS

Fixed throat, differential-type injectors create a powerful operating vacuum to drive the V10k system. Three capacity injectors are available: 3/4" for capacities up to 200 PPD (90 kgs/day), 1" up to 500 PPD (225 kgs/day), and a 2" up to 750 PPD (340 kgs/day) (not shown).

These injectors feature:

- Built-in Double Check Valves for superior protection against backflooding. A spring-loaded diaphragm with a spherical seat for positive sealing and a spring-loaded poppet check work together to maintain system integrity.
- Flexible Mounting Orientation for convenient installation. The gas inlet connection can be rotated to provide pipe entry at selected angles. The injector can also be mounted in horizontal or vertical planes. It features an integral-mounting bracket and can be disassembled for service without removal from the wall or disconnecting the inlet/outlet piping.
- Optional Anti-siphon Arrangement for swimming pools and negative backpressure applications. These injectors require a minimum inlet water pressure of 20 psi (1.4 Bar) for operation.

7.) VACUUM SWITCH

A local or remote mounted vacuum switch provides an alarm in the event of a high or low vacuum condition signifying a loss of gas feed.

TECHNICAL DATA

ACCURACY

Gas feed is $\pm 4\%$ of the indicated flow.

OPERATING RANGE

Manual 20:1 for any rotameter; Automatic 10:1.

ROTAMETERS

Choice of 5" or 10" scale length.

OPERATING VACUUM

10 to 50" water.

OPERATING TEMPERATURE RANGE

10° to 130°F (-12° to 55°C)

MOUNTING

Wall or panel mounted. Panel mounted arrangement can be configured with a panel mounted injector or a panel mounted controller (for automatic control version). An optional vacuum switch can also be mounted on the panel.

CONTROL MODES

Manual control, start-stop or program, flow proportional, direct residual and compound-loop control.

DISTANCE, SUPPLY TO CONTROL PANEL

For flexibility, it is not necessary to install the vacuum regulating valve close to the control panel. They can be a few feet to several hundred feet apart, depending on maximum feed rate, the diameter of the connecting pipe or tubing and system performance requirement.

INJECTORS

For capacities up to 200 PPD (90 kgs/day), a 3/4" injector is used. For capacities up to 500 PPD (225 kgs/day), a 1" injector is used. Injectors can be panel mounted or remote. For capacities up to 750 PPD (340 kgs/day), a 2" injector is used.

INJECTOR OPERATING WATER

This must be reasonable clean. Injectors are fixed-throat differential type. Maximum inlet pressure is 300 psi to 100°F; 150 psi to a maximum of 130°F.

PRESSURE AT APPLICATION POINT

Maximum pressure with hose or polyethylene tubing is 75 psi, but high-pressure hose or rigid pipe will allow application against backpressure of 75 to 160 psi.

ELECTRICAL REQUIREMENTS

Controller requires 120 volts $\pm 10\%$ (200 mA) or 230 volts $\pm 10\%$ (100 mA), 50/60 Hz, single phase.

OPTIONS

GAS FLOW TRANSMITTER

Non-inferential measurement of the rate of gas flow through any V10k gas feeder. Consists of a NEMA 4X sensor transmitter with a 4-20 mA output directly proportional to gas flow. See publication WT.050.114.000.UA.PS.

AUTOMATIC SWITCHOVER

A pair of vacuum-regulating valves designed to switch to a fresh gas supply from an empty container.

TON-CONTAINER KIT

Adapts the vacuum-regulating valve for mounting on a ton container for gas withdrawal.

VACUUM SWITCH

A low vacuum switch or a high, high/low vacuum switch is available to indicate loss of gas feed. Each switch contains two, s.p.s.t. contacts rated 5 amps at 250V.

TECHNICAL DATA (CONT'D)

RELATED OPTIONS

Related options include: cylinder and ton container valves and connections; header valves with manifolding and connections; vent, injector-water and injector outlet lines and clamps; main connections; solenoid valves; water-line pressure gauge; gas mask; on-line residual analyzers; residual test kits; injector vacuum gauge; spare parts; booster pumps; chlorine detector; two cylinder scale.

CHLORINE GAS WARNING

All unattended chlorine gas containers and chlorination equipment should be monitored for leaks. Sensitive chlorine detectors, which respond quickly to chlorine in the atmosphere, should be installed at each site. Request publications WT.050.130.000.UA.PS.

CARBON DIOXIDE WARNING

Because of the high pressure in carbon dioxide containers, the vacuum regulating valve cannot be mounted directly on the cylinder. A pressure-reducing valve must be installed between the cylinder and the vacuum-regulating valve.

COMPLIANCE

Gas feeder, controller and actuator are designed to conform to all applicable NEC and NEMA specifications and Chlorine Institute and Compressed Gas Association recommendations.
Overall Dimensions

CHLORINATOR:

Panel mounted:
manual: 34-5/8" x 17" x 7-5/16"
automatic: 34-5/8" x 17" x 10"

Wall mounted:
5": 12-3/8" x 13-7/16" x 6"
10": 19-7/8" x 13-7/16" x 6"

CONTROLLER:

SCU: 8-3/4" x 6-1/2" x 3-5/8"
PCU: 8-3/4" x 6-1/2" x 9-1/8"

SHIPPING WEIGHT

Wall mounted units: 10 lbs (4.5 Kgs)
Panel mounted units:
manual: 20 lbs (9.0 kgs)
automatic: 25 lbs (11 kgs)

GASES AND CAPACITIES*

| Maximum capacity | Chlorine lb/24 hour | Carbon Dioxide lb/24 hour | Sulfur Dioxide lb/24 hour | Ammonia lb/24 hour |
|---------------------|--|--|--|---|
| 5" & 10" 200 PPD | 3/10/20/30/50/ 75/100/150/200 | 2.4/8/15/24/35/5 8/75/116/150 | 3/10/20/30/50/ 75/100/150/200 | 1.4/4.5/9/14/24/ 35/45/70/95 |
| 5" & 10" 500 PPD | 3/10/20/30/50/ 75/100/150/200/250/3 00/400/500/750 | 2.4/8/15/24/35 /58/75/116/150/ 200/230/300/390 | 3/10/20/30/50/ 75/100/150/200/250/3 00/400/475 | 1.4/4.5/9/14/24/ 35/45/70/95/120/140/ 190/240 |

* A selection of tubes is also available in metric calibrations.

CONNECTIONS

Pipe and plastic tubing sizes given.

| Vacuum Regulating Valves | | | |
|--------------------------|--|------------|----------|
| Tubing to | 200 lb | 500 lb | 3000 lb |
| control panel | 3/8 x 1/2 | 1/2 x 5/8" | 1/2" NPT |
| container valve | gas inlet is yoke connection to a cylinder or header valve or, with optional adaptor, to a ton container valve | | |

| Injectors | | | |
|--------------|-------------------------------------|---|----------------------------|
| Connection | 200 lb | 500 lb | 750 lb |
| water inlet | 3/4" male NPT or 3/4" flexible pipe | 1" female NPT | 2" female NPT |
| water outlet | same as inlet | 3/4" NPT with adapters for 3/4", 1", or 1-1/2" pipe or hose | 1-1/2" male NPT or 2" hose |

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of the contract.

Wallace & Tiernan is a trademark of Siemens, its subsidiaries or affiliates. NEMA is a trademark of the National Electrical Manufacturers Association.

Siemens
Water Technologies
1901 West Garden Road
Vineland, NJ 08360
856.507.9000 phone
856.507.4125 fax
wtus.siemens.water.com
www.siemens.com/wallace-tiernan

WT.025.100.000.UA.PS.0607

©2007 Siemens Water Technologies Corp.
Subject to change without prior notice.