

# Wallace & Tiernan® Process Systems

## OSEC®-NXT

### Membrane electrochlorination system

#### Product Overview

The series of OSEC®-NXT membrane electrochlorination systems is used for commercial leisure and swimming pool applications as well as potable or industrial water treatment. They provide many safety features when used as an alternative to chlorine gas systems. Transport and handling of chlorine cylinders is completely eliminated. Only saturated brine and softened water are needed for the redeveloped electrolyzer process which safely and efficiently produces hypochlorite on-site. The optimized efficiency of the electrolyzer cells leads to a minimum demand for brine and power. The integrated Wallace & Tiernan® ChemWeb-Server data communication server provides remote visualization capability. All components for the electrolyzer process, the controller, and the water softener are skid mounted for easy installation while maintaining a small foot print. In addition, the lower capacity systems up to 6 kg (13 lb) per day contain integrated tanks for brine and sodium hypochlorite.

#### Applications

- Disinfection of swimming pool water
- Disinfection of potable, industrial and process water

#### Features

- Continuous on-line produced disinfection solution avoids by-products
- Integrated ChemWeb-Server for comfortable remote access
- Serves multiple points of injection

#### Key Benefits

- High efficiency by optimized and continuous conversion from brine to sodium hypochlorite solution
- Long life system through optimized production and integrated capacity control
- High operating safety, just requiring salt and water
- User-friendly touch panel control
- Skid mounted system for easy installation



OSEC®-NXT system for up to 60 kg Cl<sub>2</sub>/day

## Product Line Sheet

## Technical Data

Capacity Cl <sub>2</sub> /day	Dimensions W x H x D	Weight
6 kg (13.2 lbs)	1200 x 1895 x 750 mm (47.2 x 74.6 x 29.5")	448 kg (987.7 lbs)
12 kg (26.5 lbs)	1200 x 1895 x 805 mm (47.2 x 74.6 x 31.7")	340 kg (749.6 lbs)
24 kg (52.9 lbs)		390 kg (859.8 lbs)
36 kg (79.4 lbs)		440 kg (970.0 lbs)
48 kg (105.8 lbs)	1500 x 1895 x 805 mm (59.1 x 74.6 x 31.7")	490 kg (1080.3 lbs)
60 kg (132.3 lbs)	1800 x 1895 x 805 mm (70.9 x 74.6 x 31.7")	550 kg (1212.5 lbs)

For each model a detailed data sheet is available.



OSEC®-NXT system for up to 6 kg Cl<sub>2</sub>/day

Siemens  
Water Technologies

Germany  
+49 8221 9040  
wtger.water@siemens.com

United Kingdom  
+44 1732 771777  
wtuk.water@siemens.com

USA  
+1 866 766 5987  
stranco.water@siemens.com

© 2009 Siemens Water Technologies Corp.  
WT.085.135.000.IE.PS.0409  
Subject to change without prior notice.

Wallace & Tiernan and OSEC are trademarks of Siemens, its subsidiaries or affiliates.

The information provided in this brochure contains merely general descriptions of characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.